

Quick Change Hole Saw Kit



Quick Change Arbor Features:

- New arbor allows for rapid mounting or removal of hole saws.
- Faster, easier slug removal.
- Drill pilot hole without saw:
 1. Eliminates the "bite" when saw crashes into the steel.
 2. Provides better ergonomics - reduces stress on wrist, arm and hand.
 3. Eliminates obstructed view from hole saw.
- Only one arbor required from 7/8" to 6" (7/16" shank recommended for hole saws above 2-1/2").
- Works with recessed light and carbide grit hole saw products as well.
- Adapters re-usable to minimize costs.
- Universal - works with any brand hole saw.

Kit contains Bi-metal hole saws for 1/2" through 2" conduit sizes.

CAT. NO.	UPC NO.	DESCRIPTION
8300	02806	Quick Change Hole Saw Kit for 1/2" through 2" conduit sizes
02800	02800	5/16" Arbor, minimum chuck size 3/8"
02801	02801	7/16" Arbor, minimum chuck size 1/2"
02802	02802	Retrofit Kit - upgrade 3 hole saws up to 1-9/16" to Quick Change
02803	02803	Small Adapters for 9/16" to 1-9/16" saws Qty. 10
02804	02804	Large Adapters for 1-5/8" to 6" saws Qty. 3
02805	02805	Bushings for 1-1/4" to 1-9/16" saws Qty. 5

SPECIFICATIONS

Shank	Available for 3/8" and heavy duty 1/2" chuck sizes
Arbor length	5-1/2" with pilot drill
Arbor weight	0.5 lbs (227 g)
Arbor operation	Push collar to lock on saw; pull to release saw
Arbor pilot drill	3/623, 4-1/8" x 1/4" (104.8 mm x 6.4 mm)

Combination Drill/Tap Bits



- Complete hole drilling, tapping and deburring/countersinking in one operation with power drill – saves labor, time and frustration
- Back taper beyond tap to prevent thread damage from over-drilling
- Deburr/Countersink also provided on bit beyond back taper
- Made from hardened high-speed steel vs. carbon steel for longer life
- High quality hex shank to ensure strong connection to drill chuck
- Designed to tap up to 10 gauge metal
- Quick Change Adaptor included in both metric and standard kits

CAT. NO.	UPC NO.	DESCRIPTION
DTAP10-24	17613	10-24NC drill/tap bit
DTAP10-32	17614	10-32NF drill/tap bit
DTAP12-24	17615	12-24NC drill/tap bit
DTAP6-32	17611	6-32NC Drill/Tap Bit
DTAP8-32	17612	8-32NC drill/tap bit
DTAPKITM	12151	M3-M10, 6 piece drill/tap set
DTAP1/4-20	17616	1/4-20NC drill/tap bit
DTAP3/8-16	11628	3/8-16NC drill/tap bit
DTAP5/16-18	11627	5/16-18NC drill/tap bit
DTAPKIT	17620	6-32 to 1/4-20, 6 piece drill/tap set
DTAPM10C	12165	M10 X 1.50 drill/tap bit
DTAPM3C	12160	M3 X .50 drill/tap bit
DTAPM4C	12161	M4 X .70 drill/tap bit
DTAPM5C	12162	M5 X .80 drill/tap bit
DTAPM6C	12163	M6 X 1.00 drill/tap bit
DTAPM8C	12164	M8 X 1.25 drill/tap bit

SPECIFICATIONS

Material thickness	10 gauge
Material type	Mild steel, copper, brass, aluminum
Shank	1/4" quick change hex
Drill Material	Hardened, high-speed steel
Drill point	Split point with web thinning