



mpresario 1600
CONVECTAIR

TOWEL WARMER

A CAMPA PRODUCT

CAMPA

LAVA ROCK



CANPA



THE NEXT
BEST THING
TO HUMAN
WARMTH

**Natural heat
and a sizzling look.**

- Carved from a single block, this genuine lava rock panel offers a unique finish that is natural, solid and high-performance.

The solid-stone front panel evenly distributes soft, palpable radiant heat, while its high thermal mass maintains a uniform temperature throughout the room.

A fan at the bottom of the unit instantly provides additional warmth, quickly heating the entire bathroom. You'll enjoy incomparable comfort, and your towels will be toasty warm—just the way you like them!

IMPRESARIO 1600

TOWEL WARMER



HEATING ELEMENTS

- Total capacity** 1 600 W
- Radiant heat** - Radiant front panel (1) with integrated surface element (2).
- Internal high-efficiency aluminum radiant element (3).
- Fan-forced heat on demand** (4) Low-thermal-mass heating element (600 W) combined with low-pressure centrifugal blower.
- Thermal protection – Radiant** - Automatic reset overheat protection.
- **Fan-forced heat** - Resettable overheat protection. Reset by turning heater off.

TEMPERATURE CONTROL [5]

- An intelligent system that manages both radiant heating elements, for maximum comfort.
- Timer** 0-120 minutes for quick heating.
- Programmer** Control panel designed to accept the 7392 Programmer module.
Compatible with the Programmer System - Pilot wire.

CONTROL PANEL

- Location** Located on the right side of the unit.
- LCD display** screen.
- Knob 1** Timer control
- Knob 2** Temperature adjustment
- Indicator light 1** Saturated filter warning indicator light
- Indicator light 2** Heating indicator light
- Switch 1** On/Off
- Switch 2** Room temperature ventilation control

CABINET

- Front Panel** Lava rock front panel with epoxy coating; two (2) towel bars included.
- Steel construction** with polyester/epoxy anti-rust powder coating.
- Filter** Easy-to-clean, removable rear-mounted lint filter.
- Colour** BCL = Lava White

PRODUCT CHART

MODEL	Catalog N°	Colour	Power		Height		Width		Thickness		Weight	
			220-240 V	W	cm	in	cm	in	cm	in	kg	lb
Impresario 1600	7630-C16	BCL	1000-1600 W		153.5	60 ^{3/8}	42.7	16 ^{3/4}	11.4	4 ^{5/8}	37.7	83
							With bars	48	19	18	7	

INSTALLATION AND CONNECTION

Installation height 8 in (20 cm).

Clearances

Front: 20 in (50 cm)

Sides: 6 in (15 cm)

Above: 6 in (15 cm)

Installation Quick-mounted surface installation with screw-in bracket.

Connection 240-V unit: Flexible cord connection. Installation requires 2 in X 3 in wall box (not included).

Note 3-conductor cable or 2-conductor cable with a third wire should be used if unit is to be linked with the Convectair Programmer module (7392 FP).

For guaranteed, dependable operation, we recommend that all units be installed by a licensed electrical contractor. Consult convectair.com to find the most recent installation instructions for our heaters.

WARRANTY

- 2 years against all manufacturing defects†
- 5 years on heating elements

† Unless otherwise indicate

In keeping with our ongoing commitment to research and development, we reserve the right to change product specifications without notice.

IMPRESARIO.CONVECTAIR.COM

1 800 463-6478

Fax: 1 877 434-3166 (toll-free)

E-mail: support@convectair.ca

30, Carré Sicard, Sainte-Thérèse

(Québec) J7E 3X6 Canada

Disponible en français

