



## VAPOR BARRIER NON-METALLIC CABLE BOXES

Vapor Barrier Cable Boxes  
2-3/4 in. Deep, 51.0 Cu. in., 1/2 in. Setback

A83



Catalog #: 2002FBAR

### APPLICATIONS

Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside the structure. RACO® nonmetallic vapor barrier cable boxes provide the installer with a cost alternative that is lightweight and easy to install and provide excellent protection for wiring system or devices. RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires and accommodate wiring devices such as switches and receptacle.

### PRODUCT FEATURES

Self-clamping wire entry clamps  
Vapor/air barrier flange and integral wire entry seal provides superior energy savings and quick installation  
Hands free installation for 1/2", 5/8", or 3/4" drywall

### CSA

CSA C22.2 #18

### GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable  
Color: Yellow

### RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No  
Fixture (Static) Lbs.: 50

### CONFIGURATION

Cable Clamps: 12  
Bracket Type: Flush  
Bracket Setback: 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-3/4 in.

### PRODUCT MEASUREMENTS

Depth: 2-3/4 in.  
Cubic Inches (cm<sup>3</sup>): 51.0 (835.6)  
Wt. Ea. (Lbs.): 0.400  
Product Length (in.): 2.88  
Product Width (in.): 7.13  
Product Height (in.): 6.00

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 40.00  
Ship Carton Length (in.): 25.25  
Ship Carton Width (in.): 11.50  
Ship Carton Height (in.): 15.50  
Ctn Weight (Lbs.): 20.00  
Pallet Qty: 600  
UPC Number: 805035000106  
I2of5: 30805035000107