






Shown actual size: Maestro dimmer and 1-gang Claro wallplate in White (WH).


Product family features

- True multi-location dimming from every location
- Tap on to preset level; tap off; tap twice for full on; touch rocker to adjust light level
- LEDs indicate light level and glow softly in the dark
- Delayed off provides light as you exit the room
- Line frequency compensation maintains stable light levels despite power line frequency and voltage variations
- Programming allows customized functions
- C•L®, eco-dim and eco-timer models available
- Coordinating Claro®, Satin Colors®, and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates; see p. 237

Direct load type compatibility




-  Incandescent/halogen lighting
-  Dimmable CFL/LED lighting (screw-base)
-  Magnetic low-voltage lighting
-  Electronic low-voltage lighting
-  Fluorescent lighting
-  LED lighting
-  Switched lighting/fan/motor
-  Ceiling fans
-  Ceiling fan/lights

Load type requiring load interface

-  Neon/cold cathode lighting

Lighting load interfaces may be applicable for some load type, voltage, and capacity combinations. For additional information, see pp. 255–259.

Control types

-  Single-pole (one location)
-  3-way (2 locations)
-  Multi-location (up to 10 locations)

Available finishes

Use **BOLD** color code in model number (Example: MA-600-**BR**)

Gloss finishes*



WH
White



LA
Light Almond



AL
Almond



IV
Ivory



GR
Gray



BR
Brown



BL
Black

Satin Colors® finishes*



SW
Snow



LS
Limestone



BI
Biscuit



ES
Eggshell



PD
Palladium



TP
Taupe



ST
Stone



BG
Bluestone



PL
Plum



SG
Sea Glass



TQ
Turquoise



GS
Goldstone



DS
Desert Stone



GB
Greenbriar



MS
Mocha Stone



TC
Terracotta



SI
Sienna



HT
Hot



MR
Merlot



MN
Midnight



SS
Stainless Steel

Metal finish wallplate**

* Coordinating wallplates only available separately. For wallplate information, see p. 236.

** Stainless Steel wallplate only available separately and includes black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls. For wallplate information, see p. 236.

Digital fade dimmers



- Provides true dimming from each location (with companion dimmers)
- C•L® dimmer provides reliable dimming of dimmable CFLs/LEDs, as well as halogens and incandescents
- eco-dim model guarantees at least 15% energy savings compared to a standard switch*

Incandescent/halogen dimmer

Dimmable CFL/LED (screw-base) dimmer

Digital fade C•L dimmer**

Multi-location/3-way†/ single-pole 120V 600W (Inc) 150W (CFL/LED)	MACL-153M- XX ¹
---	-----------------------------------

Visit www.lutron.com/dimcflled for an approved list of dimmable CFL/LED lamps, and how to calculate wattage when mixing lamp types.

Adjustable low-end trim.

XX¹: Gloss and Satin Colors® codes, see p.57

XX²: Gloss color codes, see p.57

XX³: Satin Colors codes, see p.57

XX⁴: Available in Gloss White (WH), Ivory (IV), Almond (AL), Light Almond (LA)

Wallplates not included. Order separately, see p.236

Incandescent/halogen dimmers

Digital fade dimmers**

Multi-location/single-pole 120V 600W	MA-600- XX ²
Multi-location/single-pole 120V 600W	MSC-600M- XX ³
Multi-location/single-pole 120V 1000W	MA-1000- XX ²
Multi-location/single-pole 120V 1000W	MSC-1000M- XX ³

eco-dim digital fade dimmer**

Multi-location/single-pole 120V 600W	MA-600G- XX ⁴
---	---------------------------------

Magnetic low-voltage dimmers

Digital fade dimmers**

Multi-location/single-pole 120V 600VA (450W)	MALV-600- XX ²
Multi-location/single-pole 120V 600VA (450W)	MSCLV-600M- XX ³
Multi-location/single-pole 120V 1000VA (800W)	MALV-1000- XX ²
Multi-location/single-pole 120V 1000VA (800W)	MSCLV-1000M- XX ³

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

All models must be derated if ganged unless otherwise noted, see pp.250–252 and 254.

* Maximum light output of 85% guarantees 15% energy savings over standard switches

** Minimum load required, see specification submittal

† Works with a standard mechanical 3-way switch