

Shown above: 1-receptacle PowPak plug-in dimming module in White (MRF2-3PD-1-WH)

Available finishes

Use **BOLD** color code in model number
(Example: MRF2-3PD-1-**BL**)

Matte finishes



WH
White



BL
Black

Features and capacities

- Uses Lutron reliable Clear Connect® radio frequency (RF) technology, which provides reliable RF communication with Pico® wireless remotes (see p. 178) and Radio Powr Savr® wireless sensors (see pp.198 and 202).
- Combine up to 10 wireless devices (dimmers, switches, sensors, and/or wireless remotes)
- Easy to install, requires no wires or tools
- Available in 1- or 3-receptacle models
- Simple, button-press programming to associate with Radio Powr Savr sensors and Pico wireless remotes
- Male plug on 24 in (610mm) cord
- Female receptacle on 6 in (150mm) cord
- Communicates at 434 MHz frequency

Direct load type compatibility

PowPak plug-in dimming module (dimming mode)

- 💡 Incandescent/halogen lighting


PowPak plug-in dimming module (switching mode)

- 💡 Incandescent/halogen lighting
- 💡/💡 CFL/LED lighting (screw-base)
- 💡 Magnetic low-voltage lighting
- 🔌 Electronic low-voltage lighting

PowPak plug-in appliance module

- 🔌 General purpose

Installation



Plug-in dimming modules



- Functions much like standard lamp dimmers, and incorporates advanced features such as fade on/fade off, delayed long fade off, and rapid full on
- Can be converted into a switching module for control of other lighting loads

Plug-in appliance modules



- Switches up to 15A of general purpose load (1/2HP motor load)
- Features Lutron patented Softswitch® technology to prevent the relay contacts from arcing, extending the average life of the switch to 1,000,000 operations



Incandescent/halogen dimming modules

Plug-in dimming modules*

| | |
|--------------------------------|------------------------------------|
| 1 receptacle cord 120V 300W | MRF2-3PD-1- XX ¹ |
| 3 receptacle cord 120V 300W | MRF2-3PD-3- XX ¹ |



Switching modules

Plug-in appliance modules

| | |
|---|--------------------------------------|
| 1 receptacle cord 120V 15A (1/2HP motor) | MRF2-15APS-1- XX ¹ |
| 3 receptacle cord 120V 15A (1/2HP motor) | MRF2-15APS-3- XX ¹ |

XX¹: Matte color codes, see p. 168

* Minimum load required, see product specification for specifics