



### TYPES QA, QQA

#### QIKLUG™

A-16

For Copper Cable

Type QA heavy duty, compact, high copper alloy terminal for joining a wide range of cable to equipment pads or bar. Fast one-wrench installation. Type QQA heavy duty, high copper alloy terminal for joining cable to equipment pads or bar. Twin clamping elements secure joint vibration and flexing. One-wrench installation.



CATALOG NUMBER*		CONDUCTOR		NO. OF HOLES IN PAD	C	D	E & F	H	K	STUD HOLE SIZE	L	LL	N	T	RECOMMENDED TIGHTENING TORQUE in-lb
TYPE QA	TYPE QQA	COMMERCIAL	NAVY												
QA8C-B	QQA8C	14 SOL. - 8 STR.	4 - 14	1	9/16	9/16	—	11/16	7/32	#10	1-3/8	2-5/16	9/32	5/32	75
QA8C-2B	QQA8C-2			2		1-1/4	5/8				5/16				
QA4C-B	QQA4C	8 STR. - 4 STR.	23 - 40	1	5/8	5/8	—	3/4	9/32	1/4	1-7/16	2-3/8	5/16	3/16	110
QA4C-2B	QQA4C-2			2		1-3/16	5/8				2-15/16				
QA1C-B	QQA1C	4 STR. - 1 STR.	50 - 75	1	5/8	3/4	—	1	11/32	5/16	1-3/4	2-13/16	11/32	7/32	150
QA1C-2B	QQA1C-2			2		1-9/16	7/8				3-5/8				
QA26-B	QQA26	1/0 STR. - 2/0 STR.	100 - 125	1	13/16	1	—	1-3/16	13/32	3/8	2	3-3/16	7/16	1/4	250
QA26-2B	QQA26-2			2		1-15/16	1				4-3/16				
QA28-B	QQA28	3/0 STR. - 4/0 STR.	150 - 200	1	1	1-1/16	—	1-5/16	9/16	1/2	2-1/4	3-9/16	17/32	1/4	325
QA28-2B	QQA28-2			2		2	1				3-9/16	—	7/16		
QA28-2N*	QQA28-2N*	250 - 350	250 - 350	2 NEMA	1-3/16	3-1/8	1-3/4	1-11/16	17/32	3/8	4-5/16	5-5/8	5/8	5/16	500
QA31-B	QQA31			1		1-3/8	—				2-11/36	4-1/8	11/16		
QA31-2B	QQA31-2	400 - 500	400 - 500	2	1-3/8	1-31/32	1	2	9/16	3/8	3-3/8	—	7/16	5/16	375
QA31-2N*	QQA31-2N*			2 NEMA		3	1-3/4				4-7/16	5-7/8	5/8		
QA34-B	QQA34	600 - 800	650 - 800	1	1-3/8	1-5/8	—	2	17/32	3/8	3-3/16	4-7/8	13/16	5/16	500
QA34-2B	QQA34-2			2		2	—				3-9/16	—	7/16		
QA34-4B	QQA34-4	850 - 1000	1000	4	1-7/8	1-15/16	1	2-7/16	7/16	3/8	3-1/2	—	7/16	1/2	600
QA34-2N*	QQA34-2N*			2 NEMA		1-3/8	3-3/32				1-3/4	4-11/16	6-9/32		
QA40-B	QQA40	1100 - 1500	1300	1	1-5/8	1-7/8	—	2-3/4	11/16	5/8	3-11/16	—	1	9/16	600
QA40-2N*	QQA40-2N*			2 NEMA		3	1-3/4				4-14/16	7-3/32	5/8		
QA44-2N*	QQA44-2N	1100 - 1500	1300	4 NEMA	2-1/8	3	1-3/4	3-1/8	9/16	1/2	5	7-1/8	5/8	9/16	600
QA44-4N*	QQA44-4N*			3		3-1/16	1-3/4				—	—	5/8		
QA46-B	QQA46	1100 - 1500	1300	1	2-1/8	2-1/8	—	3-1/8	13/16	3/4	4-3/8	—	1-1/16	9/16	600
QA46-2N*	QQA46-2N*			2 NEMA		3	1-3/4				5-1/4	—	5/8		

\* "N" indicates NEMA standard stud holes.  
All 4N items ✓ See note page A-2