



Shown actual size:
Nova T☆ dimmers and
2-gang Architectural
wallplate in White (WH).

Product family features

- Can be used in conjunction with Vareo® and Nova T☆® dimmer(s) and switch(es), and Architectural accessories
- Metal and glass finish wallplates with accessory openings can also be used with Designer wallplate opening controls and Designer accessories
- All Lutron wallplates are screwless, seamless and have no visible hardware, the front plate securely snaps into the alignment adapter plate
- Blank inserts available for accessory size opening (NT-BI-)
- Customize your architectural wallplate with engraving or by adding a corporate logo. Contact customer service to get started; 1.888.LUTRON1
- Matte finish wallplates can be custom colored to perfectly match a paint color number, swatch or sample. Contact customer service to get started; 1.888.LUTRON1

Ganging and derating

- Architectural wallplates in this section use standard ganging
 - Requires fins to be removed from dimmers for proper spacing (“Fins Broken” ganging), see p. 246
 - May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, see pp. 248–249
 - Custom multi-gang wallplates required for the following cases
 - Full-capacity ganging (“No Fins Broken”)
 - Large Nova T☆ controls (1500/2000 W)
 - Nova® controls
 - Color change applications
- For further information visit
www.lutron.com/customganging.

Available finishes

Use **BOLD** color code in model number (Example: VWP-2-**SI**)

Architectural matte finishes



WH
White



LA
Light Almond



AL
Almond



BE
Beige



IV
Ivory



TP
Taupe



GR
Gray



SI
Sienna



BR
Brown



BL
Black

Architectural metal finishes*



BN
Bright Nickel



BC
Bright Chrome



CLA
Clear Anodized
Aluminum



SC
Satin Chrome




SN
Satin Nickel



QZ
Antique Bronze



AU
Gold Plated



BB
Bright Brass



BRA
Brass Anodized
Aluminum



SB
Satin Brass



QB
Antique Brass



BLA
Black Anodized
Aluminum

Architectural glass finishes**



CWH
Clear Glass



GWH
Green Glass

* Metal finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls.

** Glass finish wallplates include white plastic trim/adaptor, visible from side. Match with separate White (WH) or Snow (SW) controls

Receptacles



- Includes 1-gang wallplate

Receptacles

15A 125V	NTR-15- XX ¹
----------	--------------------------------

20A 125V	NTR-20- XX ¹
----------	--------------------------------

Tamper-resistant receptacles*

15A 125V	NTR-15-TR- XX ¹
----------	-----------------------------------

20A 125V	NTR-20-TR- XX ¹
----------	-----------------------------------

USB receptacles



- Includes two USB ports
- Ports are rated for a minimum of 10,000 insertions and removals
- Includes 1-gang wallplate

Tamper-resistant USB receptacles*

15A 125V	NTR-15-UBTR- XX ¹
----------	-------------------------------------

GFCI receptacles



- Self-testing technology allows GFCI to automatically check proper operation every 30 seconds
- LEDs indicate status of GFCI protection function
- Press reset button to reset GFCI after circuit interruption

- Includes 1-gang wallplate

Tamper-resistant, self-testing GFCI receptacles*

15A 125V, GFCI	NTR-15-GFST- XX ¹
----------------	-------------------------------------

20A 125V, GFCI	NTR-20-GFST- XX ¹
----------------	-------------------------------------

Isolated ground receptacles



- Receptacle is orange for easy ID and circuit delineation
- Model number color code is for wallplate only
- Includes 1-gang wallplate

Isolated ground receptacles*

15A 125V	NTR-15-IG-OR- XX ¹
----------	--------------------------------------

20A 125V	NTR-20-IG-OR- XX ¹
----------	--------------------------------------

XX¹: Architectural matte color codes, see p. 227 (1-gang wallplate included)

*Metal and glass finishes are only available as separate wallplates.