

Product family features

- Can be used in conjunction with the following dimmer(s), switch(es), sensor(s), and accessories: Maestro®, Maestro IR®, Maestro Wireless®, Caséta® Wireless, Pico® wireless, Diva®, Skylark Contour® and Skylark® controls, and Claro® and Satin Colors® accessories
- All Lutron wallplates are screwless, seamless, and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in Designer style opening
- Blank inserts available for Gloss (DV-BI-) and Satin Colors (SC-BI-)
- Customize your designer wallplate with engraving. Contact customer service to get started; 1.888.LUTRON1


Ganging and derating

- Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing (“Fins Broken” ganging), see p.246
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, see pp.250–252

Available finishes


Use **BOLD** color code in model number (Example: SC-1-**PL**)

Gloss finishes




WH White **LA** Light Almond **AL** Almond **IV** Ivory **GR** Gray **BR** Brown **BL** Black

Satin Colors® finishes




SW Snow **LS** Limestone **BI** Biscuit **ES** Eggshell **PD** Palladium **TP** Taupe **ST** Stone



BG Bluestone **PL** Plum **SG** Sea Glass **TQ** Turquoise **GS** Goldstone **DS** Desert Stone **GB** Greenbriar

Metal finishes*



MS Mocha Stone **TC** Terracotta **SI** Sienna **HT** Hot **MR** Merlot **MN** Midnight **SS** Stainless Steel

*Stainless Steel finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

GFCI Receptacles



- Self-testing technology allows GFCI to automatically check proper operation every 30 seconds
- LEDs indicate status of GFCI protection function
- Press reset button to reset GFCI after circuit interruption
- Wallplate sold separately

Tamper-resistant, self-testing GFCI receptacles

15A 125V, GFCI	CAR-15-GFST- XX ¹
15A 125V, GFCI	SCR-15-GFST- XX ²
20A 125V, GFCI	SCR-20-GFST- XX ²

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plug for dimming table and floor lamps
- Tamper resistant shutter mechanism

Dual dimming, tamper-resistant receptacles

15A 120/125V	CAR-15-DDTR- XX ¹
15A 120/125V	SCR-15-DDTR- XX ²
20A 120/125V	CAR-20-DDTR- XX ¹
20A 120/125V	SCR-20-DDTR- XX ²

Receptacles for half dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plug for dimming table and floor lamps
- Bottom half is a general use receptacle and will fit standard duplex plugs
- Tamper resistant shutter mechanism

Half dimming, tamper-resistant receptacles

15A 120/125V	CAR-15-HDTR- XX ¹
15A 120/125V	SCR-15-HDTR- XX ²
20A 120/125V	CAR-20-HDTR- XX ¹
20A 120/125V	SCR-20-HDTR- XX ²

XX¹: Gloss color codes, see p. 235
XX²: Satin Colors® codes, see p. 235