


Aluminum Conduit Benders

NEW!



56207

- Lightweight die-cast aluminum construction.
- The traditional Benfield® head design accurately and consistently performs common bends such as Stub Ups, Offsets, Back-to-Back and Saddle Bends.
- Bold cast-in benchmark symbols, degree scales and multiplier scales help save time on the job.
- Textured interior hook surface prevents conduit from rolling or twisting during bends.
- Wide foot pedal provides excellent stability and features angled grooves for extra traction.

Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Radius	Weight (lbs.)
56206	assembled aluminum conduit bender w/#51427 handle	1/2" (13 mm)	-	4"	4.4
56207	assembled aluminum conduit bender w/#51427 handle	3/4" (19 mm)	1/2" (13 mm)	5"	5.4

Benfield® Benders

Benfield® Powr-Jack® Benders

- Easy to read, cast-in benchmark symbols.
- Features a two-position booster step that makes it possible to bend up to 1-1/4" (32 mm) EMT, and 1" (25 mm) Rigid and IMC without expensive power tools.
- Eliminates the need for costly, pre-formed elbows.



51206

Cat. No.	Description	Thinwall/EMT	Rigid/IMC	Radius	Weight (lbs.)
51206	bender head	1-1/4" (32 mm)	1" (25 mm)	10" (254 mm)	16.50

Bender Handles



51429

- Available in multiple sizes and lengths and are compatible with all Klein Tools conduit bender heads.
- High-strength steel eliminates flex and provides excellent feel, control and leverage.
- Each handle features an enlarged diameter hollow end for inserting conduit to correct overbends.
- Bright orange color is easy to spot on the jobsite.
- Attached Benfield® bender guide includes many common bend formulas and reference points.

Cat. No.	Description:	Weight (lbs.)
51427	conduit bender handle - 38" L, 3/4" NPT tap size fits #56200 and 56201 bender heads and is replacement handle for #56206 and #56207.	3.5
51428	conduit bender handle - 44" L, 1" NPT tap size fits #56202 bender head.	6.0
51429	conduit bender handle - 54" L, 1-1/4" NPT tap size fits #51206 bender head.	8.9

All dimensions are in inches and (millimeters) unless otherwise specified.

WARNING: Always wear approved eye protection.



AEROHEAD™ Conduit Benders

Features:

Innovative AEROHEAD™ Conduit Bender head is made from an aerospace grade alloy that is up to 50% stronger and lighter than Ductile Iron.

Wide foot pedal provides excellent stability and features angled grooves for extra traction.




Bold cast-in benchmark symbols, degree scales and multiplier scales help save time on the job.

Advanced casting process precisely controls metal flow for the ultimate in core strength and ductility.

The traditional Benfield® head design accurately and consistently performs common bends such as Stub Ups, Offsets, Back-to-Back and Saddle Bends.

Cross-cut interior hook surface prevents conduit from rolling or twisting during bends.




Conduit Benders **AEROHEAD™**

Additional Features:

- High strength steel handle features a swaged end for inserting conduit to correct overbends.
- Orange color handle is easy to spot on the jobsite.
- Attached Benfield® bender guide includes many common bend formulas and reference points.

NEW!



56205

Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Radius	Weight (lbs.)
56200	AEROHEAD™ conduit bender head	1/2" (13 mm)	-	4"	1.0
56201	AEROHEAD™ conduit bender head	3/4" (19 mm)	1/2" (13 mm)	5"	2.1
56202	AEROHEAD™ conduit bender head	1" (25 mm)	3/4" (19 mm)	7"	3.6
56203	assembled AEROHEAD™ conduit bender w/#51427 handle	1/2" (13 mm)	-	4"	4.5
56204	assembled AEROHEAD™ conduit bender w/#51428 handle	3/4" (19 mm)	1/2" (13 mm)	5"	5.6
56205	assembled AEROHEAD™ conduit bender w/#51429 handle	1" (25 mm)	3/4" (19 mm)	7"	9.6

All dimensions are in inches and (millimeters) unless otherwise specified.

⚠WARNING: Always wear approved eye protection.

