

















# 3M Electrical Tapes Chart

Vinyl Electrical Tapes	Product Description/Applications	Thickness	Max. Temp.	Roll Size
<b>Scotch® Super 33+™ Professional Grade Vinyl Electrical Tape</b>  	Highly conformable, super stretchy in all weather applications; resists UV rays, abrasion, corrosion, alkalis and acids. Primary insulation for splices up to 600V. Protective jacketing.	7 mil	105°C 221°F	3/4" x 66' (19 mm x 20,1 m) 3/4" x 44' (19 mm x 13,4 m) 3/4" x 20' (19 mm x 6,0 m) 3/4" x 36 yd (19 mm x 32,9 m) 1" x 36 yd (25,4 mm x 32,9 m) 1-1/2" x 36 yd (38 mm x 32,9 m)
<b>Scotch® Heavy Duty Grade Vinyl Electrical Tape Super 88</b>  	All weather; heavy duty, professional use, abrasion resistant, fast build up. Primary insulation for splices up to 600V. Protective jacketing.	8.5 mil	105°C 221°F	3/4" x 66' (19 mm x 20,1 m) 3/4" x 44' (19 mm x 13,4 m) 3/4" x 36 yd (19 mm x 32,9 m) 1" x 36 yd (25,4 mm x 32,9 m) 1-1/2" x 36 yd (38 mm x 32,9 m) 1-1/2" x 44' (38 mm x 13,4 m) 2" x 36 yd (51 mm x 32,9 m)
<b>Scotch® Professional Grade Color Coding Vinyl Electrical Tape 35</b>  	Nine fade-resistant colors, super stretchy and conformable, excellent insulating properties. Resists abrasion, corrosion, alkalis and acid. Phase identification and marking. Harnessing.	7 mil	105°C 221°F	3/4" x 60' (19 mm x 18,2 m) 1/2" x 20' (12 mm x 6,1 m) 3/4" x 66' (19 mm x 20,1 m) 1/2" x 20' (12 mm x 6,1 m)
<b>Scotch® Extra Heavy Duty Grade Vinyl Electrical Tape 22</b>  	Thicker for increased mechanical strength and abrasion resistance. Electrical insulating. Bus bar insulation. Cable jacket repair.	10 mil	80°C 176°F	1/2" x 36 yd (13 mm x 32,9 m) 3/4" x 36 yd (19 mm x 32,9 m) 1" x 36 yd (25,4 mm x 32,9 m) 1-1/2" x 36 yd (38 mm x 32,9 m) 2" x 36 yd (51 mm x 32,9 m)
<b>3M™ Highland™ Medium Grade Vinyl Electrical Tape</b>  	Flexible, stretchy, conformable, commercial grade vinyl. Flame retardant. Protective jacketing. Harnessing. Bundling.	7 mil	90°C 194°F	3/4" x 36' (19 mm x 32,9 m) 3/4" x 66' (19 mm x 20,1 m)
<b>3M™ Temflex™ General Use Grade Vinyl Electrical Tape 1700</b> 	Economical, flexible, general purpose tape. Protective jacketing. Harnessing. Bundling.	7 mil	80°C 176°F	3/4" x 60' (19 mm x 18,2 m) 3/4" x 36 yd (19 mm x 32,9 m)
<b>3M™ Economy Tape 1400</b> 	Economical general purpose tape.	7 mil	80°C 176°F	3/4" x 60' (19 mm x 20,1 m)
<b>3M™ Temflex™ Mining Grade Vinyl Electrical Tape 1700P</b>  	Insulate and repair mining cable jacketing. Flame retardant. Printed for use in MSHA-approved splicing kits.	7 mil	80°C 176°F	3/4" x 66' (19 mm x 20,1 m) 1-1/2" x 44' (38 mm x 13,4 m) 1-1/2" x 66' (38 mm x 20,1 m)