

Project:	
Type:	
Date:	
Product Code:	
Approval:	



Performance, superiority and vapour resistant.

BFHV

Superior-grade, suspended mount fluorescent vapour proof fixture. Its unique, IP67 certified body makes it ideal in washdown or extremely dusty environments where efficiency and performance are a factor.

FEATURES

- Fibreglass body with neoprene gasket ensures a dust and water resistant seal
- · High-reflectance white reflector
- · Available with 4 or 6 lamp configurations
- Available in T5 or T8

OPTIONS

- 347V options available
- · Multi-level switching, dimmable ballast
- 4 or 6 lamps
- T5 or T8
- Cords and hanging accessories
- Occupancy and dimming controls

APPLICATIONS

- · Food processing plants
- · Manufacturing

APPROVALS

- UL certified for Canada or USA
- Meets IP67 standards
- NEMA 4X

OPTICS

Optional reflectors are available in high-reflectance white steel, white aluminum or specular aluminum. T5, T5HO and T8 fluorescent light sources are available. Standard clear acrylic lens with various options available (consult factory).

ELECTRICAL

All components have met all regulatory approvals. Fixture is available in 120 - 277VAC and 347V options. Lamp retention through rotary lamp holders.

MOUNTING

V-shaped mounting brackets for suspended applications. Surface mounting options available.

CONSTRUCTION

Fibreglass enclosure with neoprene gasket ensures a dust and water resistant seal. Clear acrylic lens ensures a maximum light path is achieved. Available with highreflectance white or specular aluminum reflector. End knock-outs allow for continuous wiring.






































PRODUCT DIMENSIONS



PRODUCT KEY

Fixture Type	Heat Management	Fixture Sizes	Number of Lamps	Lamp Watts	Lamp Type	Ballast Voltage	Ballast Factor	Options
BFHV -			—LP —	w -			-	-
	(Blank) - No Option	4	4	28	T5	120	Normal (N)	
1	- Heat Management		6	32	T8	120/277(UNV)	High (H)	
				54		347	Low (L)	

Mounting	Lens	Cords	
M16 - CT4-V Hook	L26 - Clear Polycarbonate Lens	W3XX -	Flexible Whip - 16/3 600V White (XX - Length)
M20- Ceiling Mount V-Hanger	L49 - Smooth Frosted Acrylic Lens (CT4-DIRA)	W4XX -	Flexible Whip - 16/3 600V Black (XX - Length)
M14- Mounting Beam for CT4i	L55 - Clear Acrylic Lens	W5XX -	Power Cord - 16/3 White (XX Length) NEMA Code
		W6XX -	Power Cord Set, 3-Wire 120V Plug, 14/3 (XX - Length)
Motion Sensor	Reflector	W8XX -	Power Cord Set, 3-Wire 120V Plug, 18/3 White (XX - Length)
W12 - Motion Sensor - 10C	R1 - Reflector - White Steel		
W30 - IP Rated Motion Sensor	R2 - Reflector - Full - White Aluminum 92%		
	R3 - Reflector - Full - Specular Aluminum 92%		
Dimming			
W23 - 0-10V No Leads (Standard)			
W24 - 0-10V With Leads			



















