



STANLEY® PEAR HEAD QUICK RELEASE™ RATCHETS

- Pear head design for strength, durability and performance.

Product #	Drive Size	Length
91-928	1/4 in	5-3/8 in (137 mm)
89-817	1/4 in	6-1/8 in (156 mm)
91-929	3/8 in	7-11/16 in (195 mm)
89-818	3/8 in	8 in (203 mm)
91-930	1/2 in	9-3/8 in (238 mm)
89-819	1/2 in	10-1/4 in (260 mm)



STANLEY® ROUND HEAD QUICK RELEASE™ RATCHETS

- Ratchets have an easy-to-use, thumb-operated reverse-switch mechanism.

Product #	Drive Size	Length	Handle
85-890	1/4 in	5-9/16 in (141 mm)	Smooth
87-710	1/4 in	5-5/8 in (143 mm)	Knurled
85-891	3/8 in	7-7/8 in (200 mm)	Smooth
87-715	3/8 in	7-7/8 in (200 mm)	Knurled
85-892	1/2 in	9-7/8 in (251 mm)	Smooth
87-720	1/2 in	9-7/8 in (251 mm)	Knurled
91-316	3/4 in	20 in (508 mm)	Knurled



STANLEY® ROTATOR RATCHETS

- Unique twist handle technology with 0° twist arc swing allows accessibility in tight spaces.
- 60-tooth gear system for low ratcheting arc swing and high-torque ratcheting.
- Quick release mechanism to lock sockets onto the drive during operation and allow easy changeover.
- Reversible mechanism for forward and reverse transition.
- Bi-Material ergonomic handle design for grip and comfort.

Product #	Drive Size	Length
89-961	1/4 in	7-1/4 in (184 mm)
89-962	3/8 in	9 in (227 mm)



STANLEY® 1/2" DRIVE FLEX HANDLES

- For applications where high leverage is needed to tighten or release a fastener.

Product #	Drive Size	Length	Handle
86-413	1/2 in	17-1/4 in (439 in)	Knurled
86-415	1/2 in	15 in (381 mm)	Knurled
85-710	1/2 in	14-1/8 in (359 mm)	Smooth

