#### CAT5e/6 Extenders of HDBaseT/HDMI

# KD-X200POHK



Power over HDBaseT/HDMI via Single CAT5e/6 (Tx+Rx Set) Extenders, with EDID Control, Hot Plug Control, Full Buffer System, IR Sensor, Up/Down IR or RS-232, support Ultra HD/4K & HDCP2.2

## **Key Features**

- **Power over HDBaseT:** Features power extension from Tx to Rx, Rx unit does not require power supply
- HDBaseT via Single CAT5e/6 UTP/STP Extension: With fully automatic adjustment of feedback, equalization, and amplification depending on cabling length
- > Signal Extension:
  - » Up to 150 ft. @ 4K 24/25/30(4:4:4)/60(4:2:0) using KD-CAT6STP1X cabling
  - » Up to 125 ft. @ 4K 24/25/30(4:4:4)/60(4:2:0) using third-party CAT5e/6 UTP/STP cabling
  - » Up to 250 ft. @ 1080p / 1920x1200 using KD-CAT6STP1X cabling
  - » Up to 230 ft. @ 1080p / 1920x1200 using third-party CAT5e/6 UTP/STP cabling
- **AK/Ultra HD Resolution:** Support for 4096x2160 or 3840x2160 24/25/30Hz at 4:4:4/8 Bit or 60Hz at 4:2:0/8 Bit
- > HDMI® and HDCP Licensing: Fully licensed and compatible with HDCP 2.2 and HDMI latest technology such as 4K/UHD 4:2:0/8bit at 60f/s
- **EDID Control:** Internal library features 15 default EDID configurations and native EDID data from Output/Display devices connected via Rx
- Hot Plug Detection Control: Enables integrator to choose if active signal voltage is forced to connected input devices
- > Full Buffer System™: Manages TMDS re-clocking / signal re-generation, HDCP authentication with source & display, EDID Control handshake, and Hot Plug control
- IR Sensor: Sensor powering via +5V on Rx unit's IR In port collects line-of-sight IR from remote(s) without external IR connecting block
- Up/Down IR: Two channels of IR enable control to/from devices connected to Tx and Rx units
- > RS-232: Bi-Directional control to/from Tx and Rx unit on 3.5mm connector
- Rotary Switch RS-232 Control Mode: Provides control of Tx unit as well as connectivity status







TxRx

SHOBY HENDENGEN METHOD METHOD


HDCP2.2

- **3D:** Support for standard 3D stereoscopic signal formats
- > Deep Color Support: 12bit Deep Color video / 8bit color for 4K/UHD
- Lossless compressed digital audio: Support for Dolby® TrueHD, Dolby® Digital Plus and DTS-HD Master Audio™
- CEC Support: For inter-device control between main input and output HDMI channel
- > I2C Communication: EDID and HDCP authentication to Display and Source
- Control System Support: Compatible with Compass Control®, AMX®, Control4®, Crestron®, KNX®, RTI®, Savant, URC®, Leviton® etc.

### **Specifications**

- » Inputs Tx (Each): 1 HDMI, 1 IR In
- » Outputs Tx (Each): 1 CAT5e/6 UTP/STP, 1 IR Out /RS-232 Bi-Directional
- » Inputs Rx (Each): 1 CAT5e/6 UTP/STP, 1 IR In
- » Outputs Rx (Each): 1 HDMI, 1 IR Out /RS-232 Bi-Directional
- » Regulation: CE, RoHS, WEEE
- » Enclosure: Black Metal
- » Product (Each): 4.125" x 2.625" x 0.875", Weight: 0.5 lbs
- » Shipping Carton: 6.9" x 3.9" x 3", Weight: 1.5 lbs
- » Power Supply (Tx Only): KD-PS12V2ASC, 12V/2A, 100-240VAC, 50-60Hz, Interchangeable head with screw-in connector
- » Accessories: (2) Mounting Brackets, (1) IR Emitter, (1) IR Sensor

#### System Design Example



<sup>\*</sup> For all installations, we highly recommend use of KD-CAT6STP1X STP cabling, especially in hostile electrical environments. The shield of CAT6STP must be soldered on both ends to the shield of RJ45 connector used. The CAT5/5e/6 cable has to be terminated according to TIA/EIA-568-B standard. The use of STP CAT5, 5e is not recommended.