2672 Series

2682 Series

## Non-Metallic Liquidtight Cord Connectors

## **Non-Metallic Liquidtight Flexible Cord Connectors** — Black Beauty Series

### **Application**

 A liquidtight connector to connect flexible cord to a box or enclosure and provide adequate strain relief

### **Features**

- Taper Thread hub seals in female hub (A)
- Neoprene bushing provides liquidtight installation (B)
- · Hand tightens no tools needed for assembly
- Segmented chuck provides high mechanical pullout performance will not cut or damage cord jacket (C)
- Corrosion- and weather-resistant plastic is excellent for outdoor/indoor use
- Plastic parts improve dielectric strength and provide insulated throat (D)
- Wide range reduces inventories



Body, Gland & Segmented Chuck ...... Weatherstabilized thermoplastic rated for -34° C (-29° F) to 105° C (221° F) application

Bushing.....Neoprene

#### Standard Finish


All parts as molded


### Range

.250 Outside Diameter to 1.020 Outside Diameter ...... Type S, SO, SV, ST, STO, SJ, SJO, SJT, SJTO, SVTO, SVO, SVT Flexible Cords & Cables




UL (UL File No. E-23018) CSA LR-2884, LR-4484 UL 514B CSA C22.2 No. 18 NFPA 70





2672 Series

Chuck



Typical Installation

www.tnb.com

800.816.7809

Fax: 901.252.1354




# **T&B° Fittings**

## Non-Metallic Liquidtight Cord Connectors

## Rugged, weather-stabilized nylon construction!

## **Black Beauty® Non-Metallic Liquidtight Strain-Relief Connector — Straight**





- UL 94-V2 flammability rated
- Temperature rating: -34° C to +105° C
- Meets Coast Guard CG293

CAT.	TRADE OR	THROAT		DIMENSIONS (IN.)		
NO.	HUB SIZE	DIA. (IN.)	CORD RANGE (IN.)	Α	В	C
2671	3/8"	.33	.125–.275	2.0	.90	.46
2690	1/2"	.33	.125275	2.3	.90	.60
2672	1/2"	.55	.250400	2.6	1.27	.60
2673*	1/2"	.55	.400560	2.6	1.27	.60
2691*	1/2"	.54	.560690	3.0	1.57	.60
2692*	1/2"	.54	.660780	3.0	1.57	.60
2693	3/4"	.55	.250400	2.7	1.27	.62
2694*	3/4"	.55	.400560	2.7	1.27	.62
2674	3/4"	.79	.560690	3.0	1.57	.62
2675	3/4"	.79	.660780	3.0	1.57	.62
2696*	3/4"	.76	.770895	3.2	1.89	.62
2676	1"	.98	.660780	3.3	1.89	.77
2677	1"	.98	.770895	3.3	1.89	.77
2678*	1"	.98	.870-1.020	3.3	1.89	.77
2699	1"	.98	.890-1.090	4.2	2.58	.77
2702	11/4"	1.25	.890-1.090	4.2	2.58	.80
2703	11/4"	1.25	1.080-1.280	4.0	2.58	.80
2704	11/4"	1.25	1.270-1.470	4.0	2.58	.80
2705-TB	11/2"	1.47	.890-1.150	4.2	2.95	.82
2706	11/2"	1.47	1.140-1.400	4.3	2.95	.82
2707	11/2"	1.47	1.390-1.650	4.3	2.95	.82
2708	2"	1.89	1.190-1.530	5.1	3.50	.84
2709	2"	1.89	1.520-1.860	4.9	3.50	.84

1.850-2.190

cable to permit conductors to pass thru connector body.

2"

1.89

UL File No. E 13938 CSA File No. 52391

2710\*

\*Remove sufficient outer covering of All items shown on this page are suitable for use in hazardous location where general-purpose equipment is specifically permitted by the NEC®. Class I, Div. 2. Class II, Div. 1 & 2. Class III, Div. 1 & 2.


4.9

3.50

# 90° angle with a standard-size body!

### **Black Beauty® Non-Metallic Liquidtight** Strain-Relief Connector — 90° Elbow





- Weather-stabilized nylon construction
- UL 94-V2 flammability rated
- Temperature rating: -34° C to +105° C
- Meets Coast Guard CG293

CAT.	TRADE OR	THROAT		DIMENSIONS (IN.)		
NO.	HUB SIZE	DIA. (IN.)	CORD RANGE (IN.)	Α	В	C
2680	3/8"	.33	.125275	29/32	13/4	.460
2681	1/2"	.55	.250400	_	_	_
2682*	1/2"	.55	.400560	_	_	_
2683	3/4"	.78	.560690	_	_	_
2684	3/4"	.78	.660780	_	_	_
2688	1"	.98	.560690	127/32	31/4	.770
2685	1"	.98	.660780	127/32	31/4	.770
2686	1"	.98	.770895	127/32	33/16	.770
2687*	1"	.98	.870-1.020	127/32	3	.770

thru connector body. 90° angle, standard size body.

UL File No. E 13938 CSA File No. 52391

\*Remove sufficient outer covering of All items shown on this page are suitable for use cable to permit conductors to pass in hazardous locations where general-purpose equipment is specifically permitted by the NEC. Class I, Div. 2. Class II,

Div. 1 & 2. Class III, Div. 1 & 2.



**United States** 

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354



Tel: 888.862.3289

