



SIRIUS, COMPACT STARTER, DIRECT STARTER 690 V, 110 ... 240 V AC/DC, 50 ... 60 HZ, 3 ... 12 A, IP20, CONNECTION MAIN CIRCUIT: PLUGGABLE, WITHOUT TERMINALS, CONNECTION AUXILIARY CIRCUIT: SCREW TERMINAL

| | |
|-----------------------|-----------------|
| product brand name | SIRIUS |
| Product designation | compact starter |
| Design of the product | direct starter |

| General technical data: | |
|--|--|
| Product function | |
| • Control circuit interface to parallel wiring | Yes |
| Product expansion | |
| • Auxiliary switch | Yes |
| Insulation voltage | |
| • Rated value | 690 V |
| Surge voltage resistance Rated value | 6 000 V |
| maximum permissible voltage for safe isolation | |
| • between auxiliary and auxiliary circuit | 250 V |
| • between control and auxiliary circuit | 300 V |
| • between main and auxiliary circuit | 400 V |
| Protection class IP | IP20 |
| Degree of pollution | 3 |
| Vibration resistance | f= 4 ... 5.8 Hz, d= 15 mm; f= 5.8 ... 500 Hz, a= 20 m/s ² ; 10 cycles |
| Mechanical service life (switching cycles) | |
| • of the main contacts typical | 10 000 000 |
| • of the auxiliary contacts typical | 10 000 000 |
| • of the signaling contacts typical | 10 000 000 |
| Electrical endurance (switching cycles) of the auxiliary contacts | |
| • at DC-13 at 6 A at 24 V typical | 100 000 |

| | |
|--|---|
| <ul style="list-style-type: none"> • at AC-15 at 6 A at 230 V typical | 500 000 |
| Electrical endurance (switching cycles) of the signaling contacts | |
| <ul style="list-style-type: none"> • at DC-13 at 6 A at 24 V typical | 100 000 |
| <ul style="list-style-type: none"> • at AC-15 at 6 A at 230 V typical | 500 000 |
| Type of assignment | continuous operation according to IEC 60947-6-2 |
| Equipment marking | |
| <ul style="list-style-type: none"> • acc. to DIN EN 61346-2 | Q |

Ambient conditions:

| | |
|--|----------------|
| Installation altitude at height above sea level maximum | 2 000 m |
| Ambient temperature | |
| <ul style="list-style-type: none"> • during operation | -20 ... +60 °C |
| <ul style="list-style-type: none"> • during storage | -55 ... +80 °C |
| <ul style="list-style-type: none"> • during transport | -55 ... +80 °C |
| Relative humidity during operation | 10 ... 90 % |

Main circuit:

| | |
|--|---------------------------|
| Number of poles for main current circuit | 3 |
| Adjustable response value current of the current-dependent overload release | 3 ... 12 A |
| Formula for making capacity limit current | 12 x I _e |
| Formula for interruption capacity limit current | 10 x I _e |
| Mechanical power output for 4-pole AC motor | |
| <ul style="list-style-type: none"> • at 400 V Rated value | 5.5 kW |
| <ul style="list-style-type: none"> • at 500 V Rated value | 5.5 kW |
| <ul style="list-style-type: none"> • at 690 V Rated value | 7.5 kW |
| Operating voltage | |
| <ul style="list-style-type: none"> • at AC-3 Rated value maximum | 690 V |
| Operating current | |
| <ul style="list-style-type: none"> • at AC at 400 V Rated value | 12 A |
| <ul style="list-style-type: none"> • at AC-43 <ul style="list-style-type: none"> — at 400 V Rated value — at 500 V Rated value — at 690 V Rated value | 11.5 A 12.4 A 8.9 A |
| No-load switching frequency | 3 600 1/h |
| Operating frequency | |
| <ul style="list-style-type: none"> • at AC-41 acc. to IEC 60947-6-2 maximum | 750 1/h |
| <ul style="list-style-type: none"> • at AC-43 acc. to IEC 60947-6-2 maximum | 250 1/h |

Control circuit/ Control:

| | |
|---------------------------------------|----|
| Type of voltage | AC |
| Control supply voltage 1 at AC | |

| | |
|---|--------------------------------|
| <ul style="list-style-type: none"> • at 50 Hz • at 60 Hz | 110 ... 240 V 110 ... 240 V |
| Control supply voltage 1 | |
| <ul style="list-style-type: none"> • at DC • Rated value | 110 ... 240 V 50 Hz |
| Control supply voltage frequency 2 Rated value | 60 Hz |
| Holding power | |
| <ul style="list-style-type: none"> • with AC maximum • for DC maximum | 6 W 5.1 W |

Auxiliary circuit:

| | |
|--|--------|
| Number of NC contacts | |
| <ul style="list-style-type: none"> • for auxiliary contacts | 1 |
| Number of NO contacts | |
| <ul style="list-style-type: none"> • for auxiliary contacts • of the instantaneous short-circuit release for signaling contact | 1 1 |
| Number of CO contacts | |
| <ul style="list-style-type: none"> • of the current-dependent overload release for signaling contact | 1 |
| Operating current of the auxiliary contacts at AC-12 maximum | 10 A |
| Operating current of the auxiliary contacts at DC-13 | |
| <ul style="list-style-type: none"> • at 250 V | 0.27 A |

Protective and monitoring functions:

| | |
|--|----------------------------|
| Trip class | CLASS 10 and 20 adjustable |
| OFF-delay time | 50 ms |
| Operational short-circuit current breaking capacity (Ics) | |
| <ul style="list-style-type: none"> • at 400 V • at 500 V Rated value • at 690 V Rated value | 53 kA 3 kA 3 kA |

UL/CSA ratings:

| | |
|--|---------------------------------|
| Full-load current (FLA) for three-phase AC motor | |
| <ul style="list-style-type: none"> • at 480 V Rated value • at 600 V Rated value | 12 A 12 A |
| yielded mechanical performance [hp] | |
| <ul style="list-style-type: none"> • for three-phase AC motor <ul style="list-style-type: none"> — at 200/208 V Rated value — at 220/230 V Rated value — at 460/480 V Rated value — at 575/600 V Rated value | 3 hp 3 hp 7.5 hp 10 hp |

| | |
|--|---|
| Contact rating of the auxiliary contacts acc. to UL | contacts 21-22, 13-14, 43-44 Q600 / A600, contacts 77-78 R300 / B300, contacts 95-96-98 R300 / D300 |
|--|---|

Short-circuit:

| | |
|--|------------------|
| Design of the fuse link | |
| <ul style="list-style-type: none"> for short-circuit protection of the auxiliary switch required | fuse gL/gG: 10 A |
| <ul style="list-style-type: none"> for short-circuit protection of the signaling switch of the short-circuit release required | 6A gL/gG/400V |
| <ul style="list-style-type: none"> for short-circuit protection of the signaling switch of the overload release required | 4A gL/gG/400V |

Installation/ mounting/ dimensions:

| | |
|---|--|
| mounting position | any |
| <ul style="list-style-type: none"> recommended | vertical, on horizontal standard mounting rail |
| Mounting type | screw and snap-on mounting |
| Height | 170 mm |
| Width | 45 mm |
| Depth | 165 mm |

Connections/ Terminals:

| | |
|--|---|
| Product function | |
| <ul style="list-style-type: none"> removable terminal for main circuit | Yes |
| <ul style="list-style-type: none"> removable terminal for auxiliary and control circuit | Yes |
| Type of electrical connection | |
| <ul style="list-style-type: none"> for main current circuit | plug-in without terminals |
| <ul style="list-style-type: none"> for auxiliary and control current circuit | screw-type terminals |
| Type of connectable conductor cross-section | |
| <ul style="list-style-type: none"> for main contacts <ul style="list-style-type: none"> — solid | 2x (1.5 ... 6 mm ²), 1x 10 mm ² |
| <ul style="list-style-type: none"> <ul style="list-style-type: none"> — finely stranded with core end processing | 2x (1.5 ... 6 mm ²) |
| <ul style="list-style-type: none"> for AWG conductors for main contacts | 2x (16 ... 10), 1x 8 |
| Type of connectable conductor cross-section | |
| <ul style="list-style-type: none"> for auxiliary contacts <ul style="list-style-type: none"> — solid | 0.5 ... 4 mm ² , 2x (0.5 ... 2.5 mm ²) |
| <ul style="list-style-type: none"> <ul style="list-style-type: none"> — finely stranded with core end processing | 0.5 ... 2.5 mm ² , 2x (0.5 ... 1.5 mm ²) |
| <ul style="list-style-type: none"> for AWG conductors for auxiliary contacts | 2x (20 ... 14) |

Safety related data:

| | |
|--|-----------|
| B10 value with high demand rate acc. to SN 31920 | 3 000 000 |
| Proportion of dangerous failures | |
| <ul style="list-style-type: none"> with low demand rate acc. to SN 31920 | 40 % |
| <ul style="list-style-type: none"> with high demand rate acc. to SN 31920 | 50 % |

| | |
|---|------|
| T1 value for proof test interval or service life acc. to IEC 61508 | 20 y |
|---|------|

Communication/ Protocol:

| | |
|---|----|
| Product function Bus communication | No |
|---|----|

Electromagnetic compatibility:

| | |
|--|---|
| Conducted interference due to burst acc. to IEC 61000-4-4 | 4 kV main contacts, 2 kV auxiliary contacts |
| Conducted interference due to conductor-earth surge acc. to IEC 61000-4-5 | 4 kV main contacts, 2 kV auxiliary contacts |
| Conducted interference due to conductor-conductor surge acc. to IEC 61000-4-5 | 2 kV main contacts, 1 kV auxiliary contacts |
| Conducted interference due to high-frequency radiation acc. to IEC 61000-4-6 | 0.15-80Mhz at 10V |
| Field-bound parasitic coupling acc. to IEC 61000-4-3 | 10 V/m |
| Electrostatic discharge acc. to IEC 61000-4-2 | 8 kV |
| Conducted HF-interference emissions acc. to CISPR11 | 150 kHz ... 30 MHz Class A |
| Field-bound HF-interference emission acc. to CISPR11 | 30 ... 1000 MHz Class A |

Supply voltage:

| | |
|--|----|
| Supply voltage required Auxiliary voltage | No |
|--|----|

Certificates/ approvals:

| | | |
|--------------------------|-----|---------------------------------------|
| General Product Approval | EMC | Functional Safety/Safety of Machinery |
|--------------------------|-----|---------------------------------------|



| | | |
|---------------------------|-------------------|-------------------|
| Declaration of Conformity | Test Certificates | Shipping Approval |
|---------------------------|-------------------|-------------------|



[Typprüfbescheinigung/Werkszeugnis](#)



| | |
|-------------------|-------|
| Shipping Approval | other |
|-------------------|-------|



[Umweltbestätigung](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA61201DP33>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA61201DP33>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA61201DP33&lang=en



last modified:

29.06.2015