

PE PICK OFF, CONNECTION MAIN CIRCUIT:
SPRING-LOADED TERMINAL,

General technical data:		
product brand name		SIRIUS
Product designation		PE pick-up
Protection class IP		IP20
Degree of pollution		3
Installation altitude at height above sea level maximum	m	2 000
Ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operation	°C	-20 ... +60
Vibration resistance		f = 4 to 5.8 Hz; d = 15 mm; f = 5.8 to 500 Hz; a = 2 m / s ² 10 cycles
Shock resistance		Semi-sinusoidal a = 6 m/s ² at 10 ms; 3 pos. and 3 neg. Shock in all axes
Equipment marking acc. to DIN EN 61346-2		X
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		X







Main circuit:		
Operating current with AC at 400 V Rated value	A	63

Installation/ mounting/ dimensions:		
Mounting type		plug-in fixing
Width	mm	10
Height	mm	60
Depth	mm	35

Connections/ Terminals:

Type of electrical connection for main current circuit		spring-loaded terminals
Wire stripping length for main contacts	mm	10
Connectable conductor cross-section for main contacts for load-side outgoing feeder		
• solid	mm ²	1.5 ... 10
• stranded	mm ²	1.5 ... 10
• finely stranded with core end processing	mm ²	1.5 ... 6
Type of connectable conductor cross-section for main contacts for load-side outgoing feeder		
• solid		1.5 ... 10 mm ²
• stranded		1.5 ... 10 mm ²
• finely stranded with core end processing		1.5 ... 6 mm ²
• finely stranded without core end processing		1.5 ... 6 mm ²
Type of connectable conductor cross-section for AWG conductors for main contacts for load-side outgoing feeder		16 ... 10, 1 x 8

Certificates/ approvals:

General Product Approval	EMC	Declaration of Conformity	Shipping Approval
 CSA	 UL	 EAC	 C-TICK
		 EG-Konf.	 BUREAU VERITAS

Shipping Approval	other
 DNV	 LRS
 PRS	 RINA
 RMRS	Environmental Confirmations

Safety related data:

Protection against electrical shock	finger-safe
-------------------------------------	-------------

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RA68703AC>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA68703AC>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3RA68703AC&lang=en



last modified:

27.04.2015