

EGC Static Ground Indicators

Indicates safe static ground in hazardous locations.

CEC:
Class I Division 1 and 2, Groups C, D
Class II Division 1, Groups E, F, G
Class II Division 2, Groups F, G
Class III

CEC:
CSA Enclosure Type 3R
Exia

Applications

- Static grounding indicator is connected to tanker trucks, providing a positive ground prior to the dispensing of flammable materials.
- A positive ground safeguards trucks, railcars and loading racks from the accumulation of static charge during transfer operations.
- For use in tank vehicle transfer stations classified by CEC as Class I Division 1, Groups C, D; Class II, Division 1, Groups E, F, G; Class II, Groups F, G and Class III.

Features

- Two wire positive ground indicator system renders the pumping system inoperable without a positive ground.
- Intrinsically safe ground detecting circuitry.
- Supplied standard with two LED indicator lights. Red indicates unit is on but without a positive ground. Green indicates positive ground.
- Supplied with a 7.6 meter (25 foot) cord and heavy duty self release clamp.
- Release of the ground clamp opens the contacts, stops the product flow and is indicated by the red LED pilot light.
- Circuitry will control a pump, valve or indicating device such as light or audible warning device.
- Provided with internal ground lug.
- If any electrical connections fail (either in the enclosure or at the ground rod) the red indicator light will be on and the unit will not operate and switch to green; until the problem is solved.
- An optional retractable reel is available to raise and lower static ground cable. Allows cable and clamp to hang free when not in use. The clamp should not be in contact with ground when not in use. The retractable reel is supplied with 7.6 meter (25 foot) of nylon covered steel cable and cable securing clamp.

Electrical Characteristics

- Line Voltage: 120 Vac. Control transformers for 240, 480 or 600 volt available. Contact your local representative.
- Control relay rating interlocking contact: 15 Amp at 277 Vac, 10 Amp at 600 Vac.
- Temperature limitations: +100 °C to -25 °C (+212 °F to -13 °F).

Standard Materials

- Enclosure, cover and clamp: copperfree (4/10 of 1%) aluminum
- Indicator lights: red and green LED
- All hardware (except clamp): stainless steel

Standard Finish


- Gray baked epoxy

Options

- 7.6 meter (25 foot) retractable reel.
- Breather and drain, add suffix **-BD**.
- Heater and thermostat, add suffix **-HTR**.

CEC Certifications and Compliances

- CSA Standards: C22.2 No. 14M, C22.2 No. 25, C22.2 No. 30
- CSA Certified: 038339



Appleton

CONTROLS: NEC/CEC HAZARDOUS INDICATORS AND GROUNDING DEVICES

EGC Static Ground Indicators


Indicates safe static ground in hazardous locations.

CEC:
Class I Division 1 and 2, Groups C, D
Class II Division 1, Groups E, F, G
Class II Division 2, Groups F, G
Class III


CEC:
CSA Enclosure Type 3R
Exia

Description	Catalog Number
Ground Indicator with 2 LED Indicator lights, Ground Clamp, 7.62 meters (25 feet) of cord and connector accessories (order separately)	EGC210
7.62 meter (25 foot) retractable reel	SD11N25C
Ground Clamp	EGCK1P
Ground Clamp, 7.62 meters (25 feet) of cord and connector	EGCKECC

Dimensions in Millimeters (Inches)



3/4" Conduit opening top and bottom, furnished with 3/4 - 1/2" reducers and 1/2" close-up plugs.



A	B	C	D	E	F	G	H	J	K	M	N	P	Q
232 (9.13)	244 (9.63)	359 (14.13)	425 (16.75)	184 (7.25)	184 (7.25)	51 (2.00)	70 (2.75)	95 (3.75)	70 (2.75)	191 (7.50)	384 (15.13)	10 (0.38)	44 (1.75)