


## WALL TERMINATION ANGLE/UNIVERSAL BLIND END



### Dimensions



Support and terminate runs of cable tray with this wall termination angle. Can be used as a wall support, floor to ceiling support or to safely terminate any tray run. Adapts to any configuration and any width. Available in pre-galvanized steel. Mounting hardware sold separately.

**EXPRESS TIP**

Refer to page 58 for an application example.




Tool required: 10mm nut driver

Material	Catalogue number	Weight	
		lb/ea.	kg/ea.
Pre-galvanized Steel	<b>ETA-WTA-PG</b>	0.36	0.17

## 90 DEGREE BRACKET



### Dimensions



Create high strength tee, cross and other 90 degree configurations with this 90 degree bracket. Available in hot-dipped galvanized steel either as a single bracket or a kit including one (1) bracket, four (4) bracket clamps and one (1) hot-dipped galvanized universal splice.

**EXPRESS TIP**

Refer to page 49 for an application example.



Tool required: 10mm nut driver

Description	Catalogue number	Weight	
		lb/ea.	kg/ea.
Single 90 Degree Bracket	<b>ETA-H90-HD</b>	0.62	0.28
90 Degree Bracket Kit*	<b>ETA-H90KIT-HD</b>	0.69	0.31

\* Kit includes — 1 90° bracket (ETA-H90-HD), 4 bracket clamps (ETH-WBC-HD) and 1 universal splice (ETH-SP-HD).

