



Galvanized ground rod





- Made of high strength quality steel, hot dip galvanized.
- Meets ANSI CI35.30-1979 requirements.
- Stainless steel rods are also available (**For more detailed information, contact your T&B regional sales office**).



Cat. No.	Rod Size (nominal diameter x length)				Standard Package	Weight Per 100	
	in.	ft.	mm.	m.		lb.	kg.
GR5006	1/2	x 6	12.7	x 1.8	10	410	186
GR6256	5/8	x 6	15.8	x 1.8	5	600	272
GR6258	5/8	x 8	15.8	x 2.4	5	800	363
GR6250	5/8	x 10	15.8	x 3.0	5	1000	454
GR6250B*	5/8	x 10	15.8	x 3.0	5	1000	454
GR7506	3/4	x 6	15.8	x 1.8	5	700	318
GR7508	3/4	x 8	19.0	x 2.4	5	1200	545
GR7510	3/4	x 10	19.0	x 3.0	5	1500	681

* B suffix denotes black iron bare steel ground rod (not CSA certified).
CSA lists rods 1/2" in. and larger, 10 ft. and longer.

Copper Bonded steel ground rod



- All Blackburn ground rods have a heavy uniform covering of electrolytic copper bonded to a rigid steel core.
- Copper ions are forced electrically to join with the steel core, establishing a corrosion-resistant bond between the copper and the steel.



Cat. No.	Rod Size (nominal diameter x length)				Standard Package	Weight Per 100	
	in.	ft.	mm.	m.		lb.	kg.
5005	1/2	x 5	12.7	x 1.5	5	305	138
5006	1/2	x 6	12.7	x 1.8	5	370	168
5008	1/2	x 8	12.7	x 2.4	5	545	247
5010	1/2	x 10	12.7	x 3.0	5	611	277
6256	5/8	x 6	15.8	x 1.8	5	508	230
6258*	5/8	x 8	15.8	x 2.4	5	678	308
6260*	5/8	x 10	15.8	x 3.0	5	847	384
7508*	3/4	x 8	19.0	x 2.4	5	992	450
7510*	3/4	x 10	19.0	x 3.0	5	1240	462
1010*	1	x 10	25.4	x 3.0	5	2248	1020

*Ground rods are UL listed (425H), except for regular rods shorter than 8 ft. or less than 1/2 in.
CSA lists rods 1/2" in. and larger, 10 ft. and longer.