

## Grounding

### Ground Rod Clamps



#### CIGRC58



Cat. No.	Water Pipe Size	Dimensions (in.)		Galv. Steel (in.)	Copper Clad (in.)
		Min.	Max.		
<b>Ground Rod Clamps (Bronze body / brass screws)</b>					
CIGRC58	N/A	10 sol.	2 str.	5/8	5/8
CIGRC34		8 sol.	1/0 str.	3/4	3/4

For connecting grounding conductor to either galvanized steel rod or copper clad rod  
CSA certified for wet locations and for direct burial

#### JAB12



Cat. No.	Dimensions (in.)		Dimensions (in.)				Thread Size UNC-2A
	in.	mm	Min.	Max.	Min. (mm²)	Max. (mm²)	
<b>Ground Rod Clamps</b>							
<b>Socket Type</b>							
JAB12	1/2	12.7	10 sol.	2 str.	5.2	33.6	7/16-14
JAB34C	3/4+5/8	15.8	8 sol.	3/0 str.	8.3	95.0	7/16-14
JAB1	1	25.0	8 sol.	4/0 str.	8.3	107.1	7/16-14
<b>Hex Head Bolt</b>							
JAB12H	1/2	12.7	10 sol.	2 str.	5.2	33.6	7/16-14
JAB58H	5/8	15.8	8 sol.	1/0 str.	8.3	53.4	7/16-14
JAB34H	3/4	19.0	8 sol.	1/0 str.	8.3	53.4	7/16-14
JAB1H	1	25.0	8 sol.	4/0 str.	8.3	107.1	7/16-14

Cast of high strength corrosion-resistant copper alloy  
Both hex head and socket set screw available  
Long bearing surface of clamp on ground wire secures ground connection  
UL listed for direct burial

#### G3



Cat. No.	Dimensions (in.)		Dimensions (in.)				Thread Size UNC-2A
	in.	mm	Min.	Max.	Min. (mm²)	Max. (mm²)	
<b>Type G - Budget Line Ground Rod Clamps</b>							
G3*	3/8	9.5	10 sol.	4 str.	5.2	21.1	5/16-18
G4	1/2	12.7	10 sol.	2 str.	5.2	33.6	3/8-16
G5	5/8	15.8	10 sol.	2 str.	5.2	33.6	3/8-16
G6	3/4	19.0	10 sol.	2 str.	5.2	33.6	3/8-16

A dependable ground connection offered at a substantial saving  
Cast of high strength corrosion-resistant copper alloy. Hex head bolts  
Simplified compact design will make a lasting trouble free connection  
UL listed for direct burial  
\* Not CSA certified