# Battery

### GENERAL INFORMATION


12 V 35 Ah is a general purpose battery with 3 to 5 years in standby service or more than 400 cycles at 50 % depth of discharge in cycle service.

# 57335 - 12 V 35 Ah


## SPECIFICATIONS

Nominal Voltage:		12 V	
Nominal Capacity (20 hrs):		35.0 Ah	
Dimensions			
Total Height:		178 mm (7 in.)	
Container Height:		165 mm (6 <sup>1/2</sup> in.)	
Length:		197 mm (7 <sup>3/4</sup> in.)	
Width:		132 mm (5 <sup>3/16</sup> in.)	
Weight:	Approx	10.50 Kg (23.10 lbs)	
Container Material:		UL94HB ABS UL94V-0 ABS	
Internal Resistance (25 $^\circ\text{C},77$	°F):	~18 m Ω	
Discharge Capacity Under Different Temperatures			
40 °C:		~102 %	
25 °C:		~100 %	
0 °C:		~85 %	

### **DISCHARGE CURRENT VS TIME**




#### DISCHARGE CHARACTERISTICS 25°C (77 °F)



Discharge Time

#### DIMENSIONS



mm (in.)


## CHARACTERISTICS

Capacity 25 °C / 77 °C		
20 hrs @ 1.75 A:	35 Ah	
5 hrs @ 5.6 A:	28 Ah	
1 hrs @ 21 A:	21 Ah	
1 C @ 35 A:	17.5 Ah	
Charging Voltage (25 $^{\circ}$ C, 77 $^{\circ}$ F)		
Standby Use:	13.65 V ± 0.15 V	
Cycle Use:	$14.7 V \pm 0.3 V$	
Max Discharge Current:	300 A (5 sec)	
Max Charging Current:	10.5 A	
Self-Discharge Residual Capacity (25 $^\circ$ C, 77 $^\circ$ F)		
After 3 Months:	~90 %	
After 6 Months:	~82 %	
After 12 Months:	~70 %	

#### Tolerances are +/-1/32 in. (+/-1mm) and +/-3/32 in. (+/-2mm) for height dimensions.

#### TERMINAL

mm (in.)





#### **91** Mb27960 CE

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

