

NEW! Heavy Duty Mounts and Assemblies with Wide Strap Cable Ties

Extra Heavy Tie Mounts

Panduit offers many accessories for mounting the Pan-Ty Wide Strap Extra Heavy cable ties, including: extra-heavy screw applied cable tie mounts (TMEH2). In addition to these


accessories, the Pan-Ty Wide Strap Extra Heavy cable ties are also available pre-assembled with mounting accessories: Extra Heavy Mounts.



| Part Number | Used with Cable Ties‡ | Material | Color | Environment | Mounting Method | Std Pkg. Qty | Std Ctn. Qty |
|-----------------|--|---|-------|---------------------|-----------------|--------------|--------------|
| TMEH2S5-D350 | M, I, S, HS, LH, H, EH | Impact modified heat stabilized weather resistant nylon 6.6 | Black | Outdoors or Indoors | #10 (M5) ScREW | 500 | 2,000 |
| TMEH2S6-D350 | | | | | 1/4 (M6) Screw | 500 | 2,000 |
| TMEH2S8-D350 | | | | | 5/16 (M8) Screw | 500 | 2,000 |
| TMEH2S5-3E-C350 | PLWS3EH-TL350 Wide Strap Cable Tie pre-installed | | | | #10 (M5) ScREW | 100 | 1,000 |
| TMEH2S6-3E-C350 | | | | | 1/4 (M6) Screw | 100 | 1,000 |
| TMEH2S8-3E-C350 | | | | | 5/16 (M8) Screw | 100 | 1,000 |

Screw Applied Tie Mounts

- Unique cradle design provides maximum stability for cable bundle
- Route and support large diameter and heavy cable bundles.



| Part Number | Used with Cable Ties‡ | Material | Color | Environment | Mounting Method | Std Pkg. Qty | Std Ctn. Qty |
|---------------|------------------------|---------------------------------|-------|-------------|-----------------|--------------|----------------|
| TMEH-S8-Q0 | M, I, S, HS, LH, H, EH | Weather Resistant Nylon 6.6 | Black | Outdoors | #8 (M4) Screw | 25 | 250 |
| TMEH-S10-Q0 | | | | | #10 (M5) Screw | 25 | 250 |
| TMEH-S25-Q0 | | | | | 1/4 (M6) Screw | 25 | 250 |
| TMEH-S10-C100 | | Weather Resistant Polypropylene | | | #10 (M5) Screw | 100 | 500 |
| TMEH-S10-C109 | | Polypropylene | | | Green | Indoors | #10 (M5) ScREW |

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, EH = Extra-Heavy