


# Technical Information Bulletin - LED



## ORDERING INFORMATION

Order code: 62892  
Description: LED/PAR20/7W/FL/40/D/STD/GRY/AMB  
UPC: 069549628922  
Case quantity: 48



## PERFORMANCE DATA

Shape:	PAR20
Wattage (W):	7
Lamp voltage (VAC):	120
R9:	29
Average life (L70 hours):	25 000
Initial lumens (lm)*:	380
Initial lumens per watt (lm/W):	54
CBCP:	-
CRI:	80
Beam angle:	40
Power factor:	≥ 0.96
Operating temperature range:	-20 °C/-4 °F to 45 °C/113 °F
Base:	E26

\*Initial lumens range: +/- 5 %

\*\*Typical colour temperature range: +/- 5 %



## COMPATIBLE DIMMER LIST

**LUTRON DIMMERS:** TTCL-100H-WH, D-600PH-DK, DVLV-600P-WH, NTLV-600-WH, DVELV-300P-WH, DV-603PG-WH, NLV-600-WH, CTCL-153PDH, D-603PH, TT-300NLN-WH, MRF2-3PD-1-1WH(Digital), MA-600-WH(Digital), MAW-600(Digital), MRF2-6ND-120-WH(Digital), RRD-10ND-WH(Digital), VTELV-600M-B-WH(Digital), MAELV-600-WH(Digital), MRF2-6ELV-120-WH(Digital), TG-603PGH-WH, AYLW-600P-WH, TG-603PGH-WH, S-600PR-WH, CTCL-153P-WH, MACL-153M-WH (Digital).

**OTHER DIMMERS:** Leviton C20-6683-IW, C20-6681-IW, RPI06-1LI, 6674-10W, 6615-POW, R15-IPI06-1SE, 010-IPE04-1LZ, R50-6602-IW; Legrand DRD4-B(Digital); Pass & Seymour CDLV703-P, D703-PTC, DLV703-P, CD703-PW.

## CAUTIONS

- Turn power off before inspection, installation, or removal.
  - Risk of electric shock – do not use where directly exposed to water or weather.
  - Suitable for use in open fixtures.
  - Suitable for use in damp locations.
  - Do not open – no user serviceable parts inside.
  - Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lampholder does not exceed three (3) times the minimum base diameter.
  - Use only on 120 VAC, 60 Hz circuits.
  - This device is not intended for use with emergency exit fixtures or emergency exit lights.
  - Compatible with most dimmers.
  - Three year limited warranty.
  - For complete dimmer compatibility and warranty information visit [www.standardpro.com](http://www.standardpro.com).
  - Operating temperature: -20 °C / -4 °F to 45 °C / 113 °F.
- NOTES: This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference and (2) this device must accept any interference received, including interference that may cause undesired operation. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, cULus, CSA and ANSI specifications.

Data is based upon tests performed in a controlled environment and representative of relative performance.  
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

March 6, 2015

