

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



ORDERING INFORMATION

Order code: 63300
Description: LED/CL11/15W/30K/FM/SQR/STD
UPC: 69549633001
Case quantity: 1
Luminaire description: Square LED Ceiling Luminaire

FEATURES AND SPECIFICATIONS

Lens type: Frosted Acrylic Diffuser
Lens benefits: Square design with softly contoured acrylic lenses. Installed on housing with 2 side latches.
Housing: Simple, functional and low profile design.
Applications: Ideal for use in closets, utility areas, hallways, bedrooms, offices & various residential and commercial applications.
Benefits compared to Traditional Light: Uses less energy than fluorescent lights, lasts longer and is maintenance free.



For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com

FIXTURE PERFORMANCE

Wattage (W): 15
Colour temperature (K): 3 000
CRI: 80
Average life in hours: 50 000
Lumens: 1 050
Efficacy with lens (LPW): 70
Voltage (V): 120
Hertz (Hz): 60
mili Amps (mA): 340
Beam angle: 90°
Mounting: Surface Mount/Flush-mount

POWER FACTOR (PF)

0.95

TOTAL HARMONIC DISTORTION (THD)

< 20 %

AMBIENT OPERATING TEMPERATURES

-10°C/44°F to 40°C/104°F

COMPATIBLE DIMMER LIST

COOPER: DAL06P, SAL06P and SLC03P
LEVITON: Decora – 6674 and Illuma Tech IPL06
LUTRON: Maestro MACL-153P, Diva DVCL-153P, Contour CTCL-153P


Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

November 10, 2016


ORDERING INFORMATION

Order code: 63300
 Description: LED/CL11/15W/30K/FM/SQR/STD
 UPC: 695496323001
 Case quantity: 1
 Luminaire description: Square LED Ceiling Luminaire

PHOTOMETRICS - BEAM SPREAD*



PHOTOMETRICS - CANDELA DISTRIBUTION*



PHOTOMETRICS - COEFFICIENTS OF UTILIZATION (ZONAL CAVITY METHOD)*

RCC %:	80				70				50				30				10				0
RW %:	70	50	30	0	70	50	30	0	50	30	20	0	50	30	20	0	50	30	20	0	0
RCR: 0	1.17	1.17	1.17	1.17	1.13	1.13	1.13	.90	1.06	1.06	1.06		.99	.99	.99		.93	.93	.93		.90
1	1.04	.99	.94	.89	1.01	.96	.91	.72	.89	.86	.82		.84	.81	.78		.79	.76	.74		.71
2	.94	.85	.78	.71	.91	.82	.76	.59	.77	.71	.67		.72	.68	.63		.68	.64	.61		.58
3	.86	.74	.65	.59	.82	.72	.64	.50	.67	.61	.55		.63	.58	.53		.59	.55	.51		.48
4	.78	.65	.56	.49	.75	.63	.55	.42	.60	.52	.46		.56	.50	.45		.53	.47	.43		.40
5	.72	.58	.49	.42	.69	.56	.48	.37	.53	.46	.40		.50	.44	.38		.47	.42	.37		.35
6	.66	.52	.43	.36	.63	.51	.42	.32	.48	.40	.35		.45	.39	.34		.43	.37	.32		.30
7	.61	.47	.38	.32	.59	.46	.37	.28	.43	.36	.31		.41	.35	.30		.39	.33	.29		.27
8	.57	.43	.34	.28	.55	.42	.34	.25	.40	.32	.27		.38	.31	.26		.36	.30	.26		.24
9	.53	.39	.31	.25	.51	.38	.30	.23	.36	.29	.24		.35	.28	.24		.33	.27	.23		.21
10	.50	.36	.28	.23	.48	.35	.28	.21	.34	.27	.22		.32	.26	.21		.31	.25	.21		.19

CAN ICES-005 (B) / NMB-005 (B)

This lighting equipment complies with Canadian standard ICES-005; for use in commercial applications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.


ORDERING INFORMATION

Order code: 63300
 Description: LED/CL11/15W/30K/FM/SQR/STD
 UPC: 69549633001
 Case quantity: 1
 Luminaire description: Square LED Ceiling Luminaire

DIMENSIONS

Length: 11" (27.94 cm)
 Diameter: -
 Height: 3.5" (8.89 cm)
 Depth: 3.5" (8.89 cm)

TECHNICAL DRAWINGS



WARNINGS

- Installation and maintenance must be performed by licensed electricians only.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.

WARNING – Risk of electric shock. Suitable for damp locations.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____