

ORDERING INFORMATION

Order code: 63636
 Description: LED/T8/17W/840/48/STD
 UPC: 69549636361
 Case quantity: 25



Nominal length : 48 in. (1 220 mm) Dia. : 1 in. (26 mm)

PERFORMANCE DATA

Shape: T8
 Wattage (W): 17
 Base: G13
 Starting method: Instant Start (IS)
 Lamp voltage (VAC): 120 V-277 V/ 347 V
 Color temperature (K)**: 4 000
 Average life (L70 hours): 50 000
 Initial lumens (lm)*: 2 200
 CRI: 82
 Beam angle: 230
 Operating temperature range: -20°C / 4°F to 45°C / 113°F

*Initial lumens range: +/- 5 %

**Typical colour temperature range: +/- 5 %



For a complete list of DLC qualified products, please visit www.standardpro.com

Order code	Average System Watts (W)			Initial Lumens (lm)		
	LBF	NBF	HBF	LBF	NBF	HBF
63636	17.70	20.20	26.70	1 990	2 300	2 930

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Do not use with dimmers.
- Operates on instant start electronic ballasts only.
- Please refer to www.standardpro.com for a complete list of compatible ballasts.
- Use only in dry locations.
- Any modifications to this product will void the warranty.

NOTES: This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference and (2) this device must accept any interference received, including interference that may cause undesired operation. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, cULus, CSA and ANSI specifications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

June 12, 2015