

## Wallplate families

### Rugged design and quality materials make Arrow Hart wallplates the best choice

Whether faced with a commercial, institutional or industrial setting, you will find the desired material, configuration, style, size and color you need



**Standard size**  
Wallplates for precision cuts



**Mid-size and oversize**  
Wallplates for applications that require additional wall coverage



**Extra depth**  
Wallplates to provide a flush fit to the wall when an old work outlet box is used



#### Specification grade thermoplastic

- Available in both nylon and polycarbonate constructions
- Virtually unbreakable plates reduce installation and replacement costs
- Preferred for industrial, institutional, and other high-traffic areas
- Exclusive time-saving screw catch feature holds mounting screws captive and simplifies installation
- High gloss finish is soil-resistant
- Available in standard size and mid-size configurations with screwless and pre-marked special use versions available



#### Specification grade metal wallplates

- Constructed of non-corrosive 302/304 Stainless steel, brass or chrome
- Available in standard, mid-size, and oversize configurations with pre-marked special use versions available
- 302/304 Stainless steel is non-magnetic and non-corrosive for rugged durability
- Solid brass is coated with transparent lacquer to resist premature oxidation
- Shipped with removable protective film
- Recommended for industrial, institutional and commercial applications

## Same style, same durable quality with CuVerro® antimicrobial copper surfaces

The Arrow Hart line of devices featuring CuVerro® antimicrobial copper surfaces, offer specification grade decorator switches and wallplates in multiple gangs and configurations

### Features & benefits



**Wallplates with CuVerro® antimicrobial touch surface**



Antimicrobial Copper **Cu<sup>+</sup>**

- Touch surfaces constructed of EPA registered<sup>++</sup> CuVerro® antimicrobial copper
- When cleaned regularly, delivers continuous and ongoing antibacterial<sup>+</sup> action, remaining effective in killing greater than 99.9% of bacteria<sup>+</sup> within 2 hours
- Unlike coatings, CuVerro® surfaces are wear resistant and the durable antibacterial<sup>+</sup> properties will remain effective for as long as the product remains in place and is used as directed
- Tarnish resistant with minimal color change over time
- Surfaces should be cleaned to regular protocols
- Durable enough for hospital grade cleaners

<sup>+</sup>Laboratory testing shows that, when cleaned regularly, CuVerro® antimicrobial copper surfaces kill greater than 99.9% of the following bacteria within 2 hours of exposure: MRSA, Staphylococcus aureus, Enterobacter aerogenes, Pseudomonas aeruginosa, and E. coli O157:H7. CuVerro® antimicrobial copper surfaces are a supplement to and not a substitute for standard infection control practices and have been shown to reduce microbial contamination, but do not necessarily prevent cross contamination; users must continue to follow all current infection control practices, including those practices related to cleaning and disinfection of environmental surfaces. CuVerro® is a registered trademark of GBC Metals, LLC and is used with permission, CW-0013-1207.

<sup>++</sup>EPA Registration Number 85353-5 (7600CUR Series) and 85353-3 (7600CU Series)







**Compliances, specifications and availability are subject to change without notice.**

[www.eaton.com](http://www.eaton.com)  
[www.eaton.com/arrowhart](http://www.eaton.com/arrowhart)

### Mid-size sectional wallplates

#### Product description

1-Gang



#### Sectional wallplates

Description	Material	Location	Color	Catalog no.	
1-Gang toggle	Polycarbonate	Center	W	<input type="checkbox"/> STC1W	•
		End	W	<input type="checkbox"/> STE1W	•
1-Gang decorator	Polycarbonate	Center	W	<input type="checkbox"/> STC26W	•
		End	W	<input type="checkbox"/> STE26W	•
1-Gang duplex receptacle	Polycarbonate	Center	W	<input type="checkbox"/> STC8W	•
		End	W	<input type="checkbox"/> STE8W	•
1-Gang blank	Polycarbonate	Center	W	<input type="checkbox"/> STC14W	•
		End	W	<input type="checkbox"/> STE14W	•
1-Gang single receptacle 1.40" (35.7mm) hole	Polycarbonate	Center	W	<input type="checkbox"/> STC7W	•
		End	W	<input type="checkbox"/> STE7W	•

### Mid-size pre-marked special use wallplates

#### Product description

1-Gang, 2-Gang

#### Pre-marked special use

Description	Material	Color suffix	Catalog no.	
1-Gang toggle "emergency"	Polycarbonate	RD	<input type="checkbox"/> PJ1EM	•
1-Gang decorator "emergency"	Polycarbonate	RD	<input type="checkbox"/> PJ26EM	•
1-Gang orange decorator "isolated ground"	Polycarbonate	RN	<input type="checkbox"/> PJ26IG	•
1-Gang orange single receptacle, 1.40" (35.7mm) hole "isolated ground"	Polycarbonate	RN	<input type="checkbox"/> PJ7IG	•
1-Gang duplex receptacle "computer"	Polycarbonate	V, W	<input type="checkbox"/> PJ8CO_	•
1-Gang duplex receptacle "emergency"	Polycarbonate	RD	<input type="checkbox"/> PJ8EM	•
1-Gang duplex receptacle "GFCI protected"	Polycarbonate	V, W	<input type="checkbox"/> PJ8GF_	•
1-Gang orange duplex receptacle "isolated ground"	Polycarbonate	RN	<input type="checkbox"/> PJ8IG	•
2-Gang toggle "emergency"	Polycarbonate	RD	<input type="checkbox"/> PJ2EM	•
2-Gang duplex receptacle "emergency"	Polycarbonate	RD	<input type="checkbox"/> PJ82EM	•

#### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: RD (Red), RN (Orange), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

RoHS compliant - Page Q-32