# Technical Information Bulletin - LED



Date: In hands date of project: Project name/Number: Name of distributor: Client #: Name of end user:

# Diameter 힣

#### ORDERING INFORMATION

Order code: 64636

**Description:** LED/GU10/7W/30K/38/ELUME

UPC: 69549646360

Case quantity: 48

# MOL: 2 3/32 in. (53.5 mm)

**DIMMER COMPATIBILITY LIST** 

AAL06, SLC03P

CTCL-153P, DVCL-153P

HCL453P

Duiss

6674, IPL06

Legrand

Cooper

Leviton

Lutron

Dia.: 1 15/16 in. (49 mm)

## PERFORMANCE DATA

**MR16** Shape: Base: **GU10** Wattage (W): 7 Lamp voltage (VAC): 120 Colour temperature (K)\*\*: 3 000 Average life (L70 hours): 25 000 Initial lumens (lm)\*: 553 Initial lumens per watt (lm/W): 79 CRI: 84 Beam angle: 38 Power factor: 0.99

Operating temperature range: - 20 °C / -4 °F to 45 °C / 113 °F

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 5 %

















### **CAUTIONS**

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather.
   Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.

- Do not open no user serviceable parts inside.
   Use only on 120 VAC, 60Hz circuits.
   This device is not intended for use with emergency exit fixtures or emergency exit lights. Compatible with most dimmers.
  For complete dimmer and warranty information visit www.standardpro.com.

Description

- Not recommended for use with timers.
  Operating temperature: 20 °C / 4 °F to 45 °C / 113 °F.
  3 Years Limited Warranty.

Qty	Description	Price	
		'	
I accept the specif	ications of the lamp configuration mentione	d above.	
Name:			
Company:			
Signature:		 Date:	

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



A+.