

ORDERING INFORMATION


Order code: 63601
 Description: LED/BR30/9.5W/27K/STD
 UPC: 069549636019
 Case quantity: 20

PERFORMANCE DATA

Shape: BR30
 Wattage (W): 9.5
 Base: E26
 Lamp voltage (VAC): 120
 Colour temperature (K)**: 2 700
 Average life (L70 hours): 25 000
 Initial lumens (lm)*: 650
 Initial lumens per watt (lm/W): 68
 CRI: 80
 Beam angle: 120
 Power factor: 0.9
 Operating temperature range: -20 °C /-4 °F to 40 °C /104 °F

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 5 %



MOL : 5 3/16 in. (135 mm) Dia. : 3 3/4 in. (95 mm)

For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com.

COMPATIBLE DIMMER LIST

Legrand: HCL453P
 Cooper: DAL06P, SAL06P, SLC03P
 Leviton: DSM10-1LZ
 Lutron: CTCL-153P, DVELV-300P, SELV-300P, NTELV-600

CAUTIONS

- Risk of electric shock, for use in dry locations only.
- Suitable for use in open luminaires.
- For complete dimmer compatibility and warranty information visit www.standardpro.com
- Operating temperature: -20 °C/-4 °F to 40 °C/104 °F

NOTES: This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. This product may cause interference with other devices. If interference occurs, change the location of the product. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, cULus, CSA and ANSI specifications.