


Technical Information Bulletin - LED

E-Lume™

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



MOL : 2 1/8 in. (54 mm) Dia. : 1 3/32 in. (50 mm)

ORDERING INFORMATION

Order code: 65394
 Description: LED/GU10/5W/30K/40/GLASS/ELUME
 UPC: 69549653948
 Case quantity: 100

PERFORMANCE DATA

Shape: MR16
 Base: GU10
 Wattage (W): 5
 Lamp voltage (VAC): 120
 Colour temperature (K)**: 3 000
 Average life (L70 hours): 25 000
 Initial lumens (lm)*: 544
 Initial lumens per watt (lm/W): 109
 CRI: 82
 Beam angle (°): 40
 Power factor: 0.9
 Operating temperature range: - 25 °C / -13 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %



This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.
- 3 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

DIMMER COMPATIBILITY LIST

Legrand	HCL453P
Cooper	AAL06, DAL06P, SLC03P
Leviton	6615, 6674, DSL06-1LZ, IPE04-1LZ, IPL06
Lutron	AYCL-253P, CTCL-153P, DVCL-153P, DVCL-253P, DVELV-300P, NTELV-600, SELV-300P