

Thermal Transfer Military Grade Single-Sided Heat Shrink Labels

- Permanent, one-piece, heat shrink sleeve designed to provide clear, durable identification of wires and cables
- Meet UL Standard 224 with a VW-1 rating for flammability and AMS-DTL-23053/5C (Class 1 and Class 3)
- Meet SAE-AS81531, MIL-STD-883F Method 2015.13, Solutions A, B, and D, and MIL-STD-202G Method 215K, Solutions A, C, and D when printed with resin and hybrid thermal transfer ribbons
- Shrink ratio 3:1
- Tested for use as an identification marker in (Class 1E) harsh environments
- Use thermal transfer hybrid ribbon or white resin ribbon
- Temperature range: -67°F to 275°F (-55°C to 135°C)
- UL224 recognized, File # E205133; CSA certified, C22.2 No. 198.1.06, File # 256205



Part Number	Part Number	Diameter		Width		Height		Min. Cable O.D.		Max Cable O.D.		Wire Range	Labels Per Row	Labels Per Roll	Std. Pkg. Qty. (Roll)
		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm				
H050X025H1T*+	H050X025H2T	0.13	3.1	0.50	12.7	0.25	6.4	0.04	1.0	0.13	3.3	22 – 18 AWG	4	2000	1
H075X025H1T*+	H075X025H2T			0.75	19.1								2	1000	
H100X025H1T*+	H100X025H2T			1.00	25.4								1	500	
H150X025H1T*+	H150X025H2T			1.50	38.1										
H200X025H1T*+	H200X025H2T			2.00	50.8										
H050X034H1T*+	H050X034H2T	0.19	4.7	0.50	12.7	0.34	8.6	0.06	1.5	0.19	4.8	18 – 12 AWG	4	2000	
H075X034H1T*+	H075X034H2T			0.75	19.1								2	1000	
H100X034H1T*+	H100X034H2T			1.00	25.4								1	500	
H150X034H1T*+	H150X034H2T			1.50	38.1										
H200X034H1T*+	H200X034H2T			2.00	50.8										
H050X044H1T*+	H050X044H2T	0.25	6.3	0.50	12.7	0.44	11.2	0.08	2.0	0.25	6.4	16 – 10 AWG	4	2000	
H075X044H1T*+	H075X044H2T			0.75	19.1								2	1000	
H100X044H1T*+	H100X044H2T			1.00	25.4								1	500	
H150X044H1T*+	H150X044H2T			1.50	38.1										
H200X044H1T*+	H200X044H2T			2.00	50.8										
H050X064H1T*+	H050X064H2T	0.38	9.7	0.50	12.7	0.64	16.3	0.13	3.3	0.38	9.7	12 – 6 AWG	4	2000	
H100X064H1T*+	H100X064H2T			1.00	25.4								2	1000	
H200X064H1T*+	H200X064H2T			2.00	50.8								1	500	
H050X084H1T	—	0.50	12.7	0.50	12.7	0.84	21.3	0.17	4.3	0.50	12.7	8 – 1 AWG	4	2000	
H100X084H1T+	H100X084H2T			1.00	25.4								2	1000	
H200X084H1T+	H200X084H2T			2.00	50.8								1	500	
H050X165H1T	—	1.00	25.4	0.50	12.7	1.65	41.9	0.33	8.4	1.00	25.4	4 AWG – 500 MCM	4	1000	
H100X165H1T+	H100X165H2T			1.00	25.4								2	500	
H200X165H1T+	H200X165H2T			2.00	50.8								1	250	
H200X240H1T	H200X240H2T	1.50	38.1	2.00	50.8	2.40	61.0	0.50	12.7	1.50	38.1	1 AWG – 1000 MCM	1	100	

Order number of labels required in multiples of Standard Package Quantity.
 *Available in Bulk packages (5 times Labels Per Roll), add -B to end of part number
 +Available in two additional colors, replace suffix H1T with (H3T) Black or (H4T) Red