


# STRAIGHT BLADE RECEPTACLES

## PlugTail™ Specification Grade Receptacles

### PTTR5362W and PT5362SCI PlugTail™ Spec Grade Receptacles


- A. Auto-ground clip** assures positive ground.
- B. .036 inch thick, brass, triple-wipe power contacts** for lasting retention.
- C. Dual mechanical shutter system** to help prevent insertion of foreign objects.
- D. Plated steel wrap strap design** for maximum durability and corrosion resistance.
- E. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
- F. Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
- G. Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
- H. Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.
- I. No exposed terminals** create a finger safe application before, during, and after installation.
- J. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
- K. Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
- L. Exclusive patented feature, circuit label on back** allows permanent circuit identification.
- M. Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
- N. Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.
- O. Auto-ground clip** assures positive ground.
- P. .036 inch thick, brass, triple-wipe power contacts** for lasting retention.
- Q. Plated steel wrap strap design** for maximum durability and corrosion resistance.
- R. Pre-wired with one welded pre-stripped wire lead** to facilitate switched receptacle circuit applications.

**Three drive screws anchor strap** to back body and face.




## STRAIGHT BLADE RECEPTACLES

## PlugTail™ Specification Grade Receptacles Split Circuit 15 &amp; 20A, 125V




## Features

- Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap-around strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE	
	A.	V.			 US UL498	FSUL WC596
SPLIT CIRCUIT DUPLEX RECEPTACLES WITH 6" LEAD						
PT5262SCI	15	125	Ivory	5-15R	•	•
PT5262SCW	15	125	White	5-15R	•	•
PT5262SC	15	125	Brown	5-15R	•	•
PT5262SCGRY	15	125	Gray	5-15R	•	•
PT5262SCBK	15	125	Black	5-15R	•	•
PT5262SCRED	15	125	Red	5-15R	•	•
PT5262SCLA	15	125	Light Almond	5-15R	•	•
PT5262SCBL	15	125	Blue	5-15R	•	•
PT5362SCI	20	125	Ivory	5-20R	•	•
PT5362SCW	20	125	White	5-20R	•	•
PT5362SC	20	125	Brown	5-20R	•	•
PT5362SCGRY	20	125	Gray	5-20R	•	•
PT5362SCBK	20	125	Black	5-20R	•	•
PT5362SCRED	20	125	Red	5-20R	•	•
PT5362SCLA	20	125	Light Almond	5-20R	•	•
PT5362SCBL	20	125	Blue	5-20R	•	•

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE	
	A.	V.			 UL498	FSUL WC596
TAMPER-RESISTANT SPLIT CIRCUIT DUPLEX RECEPTACLES WITH 6" LEAD						
PTTR5262SCI	15	125	Ivory	5-15R	•	•
PTTR5262SCW	15	125	White	5-15R	•	•
PTTR5262SC	15	125	Brown	5-15R	•	•
PTTR5262SCBK	15	125	Black	5-15R	•	•
PTTR5262SCLA	15	125	Light Almond	5-15R	•	•
PTTR5362SCI	20	125	Ivory	5-20R	•	•
PTTR5362SCW	20	125	White	5-20R	•	•
PTTR5362SC	20	125	Brown	5-20R	•	•
PTTR5362SCBK	20	125	Black	5-20R	•	•
PTTR5362SCLA	20	125	Light Almond	5-20R	•	•

## 2 Pole, 3 Wire




For Bulk Packaging Solutions consult factory.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory

Light Almond


White

Green

Antique Brass

Dark Bronze

Nickel



Black

Blue

Brown

Gray


Orange

Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates

#### Metal Finish



Aluminum

Brass (Brushed)

Polished Brass


Stainless Steel

Brushed Bronze

Chrome

### Custom Metal Wall Plates Paint Finish Colors

#### Paint Color



Orange

Green

Gray

Yellow

Glossy Black

Brown

White



Primer

Red

Pink

Flat Black

Ivory

Light Almond

Blue

To order custom metal wall plates, see Pages P-40 – P-44.

**For additional colors consult factory.**