MECHANICAL BENDERS


SITE-RITE® Hand Benders for 1/2"-11/4" EMT and 1/2"-1" Rigid/IMC conduit



- · Superior, patented Site-Rite® sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light.
- Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight.
- Strong, stable square hook design.
- 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage.
- 1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage.
- All the bender handles are a consistent diameter, offering a bigger grip area, while still straight up and down for fast 30 degree bends.
- Lifetime Limited Warranty.

SITE-RITE® Iron Heads 840F, 841F, 842F, 843F

| CAT. NO. | UPC NO. | DESCRIPTION | WEIGHT |
|----------|---------|---|--------------------|
| 840A | 12810 | Aluminum Hand Bender Head for 1/2" EMT | 1.4 lbs.(0.7 kg) |
| 841A | 12838 | Aluminum Hand Bender Head for 3/4" EMT, 1/2" Rigid/IMC | 2.1 lbs. (0.9 kg) |
| 842A | 12839 | Aluminum Hand Bender Head for 1" EMT, 3/4" Rigid/IMC | 3.5 lbs. (1.6 kg) |
| 843A | 12524 | Aluminum Hand Bender Head for 1-1/4" EMT, 1" Rigid/IMC | 8.3 lbs. (3.8 kg) |
| 840AH | 12676 | Aluminum Hand Bender Head with Handle for 1/2" EMT* | 5.5 lbs. (2.5 kg) |
| 841AH | 12677 | Aluminum Hand Bender Head with Handle for 3/4" EMT, 1/2" Rigid/IMC* | 6.4 lbs. (2.9 kg) |
| 842AH | 12678 | Aluminum Hand Bender Head with Handle for 1" EMT, 3/4" Rigid/IMC* | 11 lbs. (5 kg) |
| 840F | 12831 | Iron Hand Bender Head for 1/2" EMT 1 | 3.1 lbs. (1.4 kg) |
| 841F | 12832 | Iron Hand Bender Head for 3/4" EMT, 1/2" Rigid/IMC | 4.3 lbs. (2.0 kg) |
| 842F | 12833 | Iron Hand Bender Head for 1" EMT, 3/4" Rigid/IMC | 7.2 lbs. (3.3 kg) |
| 843F | 12834 | Iron Hand Bender Head for 1-1/4" EMT, 1" Rigid/IMC | 16.2 lbs. (7.3 kg) |
| 840FH | 12835 | Iron Hand Bender Head with Handle for 1/2" EMT* | 7 lbs. (3.2 kg) |
| 841FH | 12836 | Iron Hand Bender Head with Handle for 3/4" EMT, 1/2" Rigid/IMC* | 9 lbs. (4.1 kg) |
| 842FH | 12837 | Iron Hand Bender Head with Handle for 1" EMT, 3/4" Rigid/IMC* | 15 lbs. (6.8 kg) |
| 84H1 | 12689 | Handle for 1/2" & 3/4" Aluminum or Iron Hand Bender Heads | 4.5 lbs. (2.0 kg) |
| 84H2 | 12690 | Handle for 1" Aluminum or Iron Hand Bender Heads | 7.3 lbs. (3.3 kg) |
| 84H3 | 12691 | Handle for 1-1/4" Aluminum or Iron Hand Bender Heads | 11.5 lbs. (5.2 kg) |



| | CENTERLINE BENDING RADII | | | | |
|--|--------------------------|--------------|---------------------|-------------|-------------|
| | EMT | RIGID IMC | CENTERLINE RADII | ALUMINUM | IRON |
| | 1/2" | | 4-3/16" (106.5 mm) | 840A, 840AH | 840F, 840FH |
| | 3/4" | 1/2" | 5-1/8" (130.2 mm) | 841A, 841AH | 841F, 841FH |
| | 1" | 3/4" | 6-1/2" (165.1 mm) | 842A, 842AH | 842F, 842FH |
| | 1-1/4" | 1" | 9-5/8" (244.5 mm) | 843A | 843F |

HICKEYS with Welded Handles for 1/2" - 1" Rigid conduit



- Heavy-duty cast steel head.
 - Welded steel handle.
- Bend tight radius stub-ups.

| CAT. NO. | UPC NO. | DESCRIPTION | WEIGHT |
|----------|---------|-----------------------|--------------------|
| 508 | 18102 | Hickey for 1/2" Rigid | 6.9 lbs. (3.1 kg). |
| 512 | 18103 | Hickey for 3/4" Rigid | 8 lbs. (3.6 kg). |
| 516 | 18104 | Hickey for 1" Rigid | 13 lbs. (5.9 kg) |

