

## Flat-Steel Fish Tape- 1/4" Wide



- Flat steel tape reaches easily above ceilings, under carpets, and through walls to install wire.
- 25' (7.6 m) long, extending your reach.
- Winder case with crank handle for easy, compact storage.

CAT. NO.	UPC NO.	DESCRIPTION
438-2X	01696	25' x 1/4" x 0.030" (7.6 m x 6.4 mm x 0.8 mm) Steel Fish Tape

### SPECIFICATIONS

**Weight** 1.25 lb (0.6 kg)

## MagnumPRO™ Stainless Steel Fish Tapes - 1/8" Wide

**NEW**



- Corrosion free stainless steel tape for maximum life.
- Fish further and faster with Speed Flex leader.
- Advanced comfort handle grip reduces fatigue.
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly.
- Rugged case design improves drop impact capability.
- Flared case with Grip Ridges for no slip handling.
- Available in 100' (30.5 m) and 200' (61 m) lengths.
- Replacement Speed Flex leader.

CAT. NO.	UPC NO.	DESCRIPTION
FTSS438-100	12711	Stainless Steel Fish Tape - 100' x 1/8" (30.5 m x 3.2 mm)
FTSS438-200	12712	Stainless Steel Fish Tape - 200' x 1/8" (61 m x 3.2 mm)
RSS438-100	12480	<b>R</b> Replacement Stainless Steel Tape - 100' (NO CASE)
RSS438-200	12481	<b>R</b> Replacement Stainless Steel Tape - 200' (NO CASE)
439-2	14392	<b>R</b> 12" (305 mm) SPEED FLEX Leader (solder joints)
10052	10052	<b>R</b> 12" Case/Handle Replacement Kit

### SPECIFICATIONS

**Capacity** 1/8" (3.2 mm) tape width-400 lbs. (1.7 kN) maximum design strength  
**Weight** FTSS438-100 - 4.8 lbs. (2.2 kg);  
 FTSS438-200 - 7.4 lbs. (3.4 kg)

## MagnumPRO™ Flexible Steel Fish Tapes

**NEW**



- Multi-strand steel cable for maximum flexibility.
- Available in 50' (15.2 m) and 100' (30.5 m) lengths.
- Advanced comfort handle grip reduces fatigue.
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly.
- Rugged case design improves drop impact capability.
- Flared case with Grip Ridges for no slip handling.

CAT. NO.	UPC NO.	DESCRIPTION
FTFS439-50	12713	Flexible Steel Fish Tape - 50' x 3/16" (15.2 m x 4.8 mm)
FTFS439-100	12714	Flexible Steel Fish Tape - 50' x 3/16" (30.5 m x 4.8 mm)
FS439-100	12482	Flexible Steel Fish Tape - 50' x 3/16" (15.2 m x 4.8 mm) Double Tip (NO CASE)
10052	10052	<b>R</b> 12" Case/Handle Replacement Kit

### SPECIFICATIONS

**Capacity** 3/16" (4.8 mm) tape width - 500 lbs. (2.2 kN) maximum design strength.  
**Weight** FTFS439-50 - 5.6 lbs. (2.5 kg);  
 FTFS439-100 - 8.9 lbs. (4.0 kg);  
 FS439-100 - 6.2 lbs. (2.8 kg)

Fishing

USA

Tel: 800.435.0786  
 Fax: 800.451.2632

CANADA

Tel: 800.435.0786  
 Fax: 800.524.2853

INTERNATIONAL

Tel: +1.815.397.7070  
 Fax: +1.815.397.9247