

Flexible metallic conduit fittings

Squeeze type – malleable iron

SQUEEZE TYPE – MALLEABLE IRON

Applications:

- Used to squeeze and secure AC/MC cable to a box or enclosure

Features:

- High strength malleable iron
- 105°C temperature rating
- Used with armored cable and flexible metal conduit
- Male threads – NPSM

Standard materials:

- Malleable iron
- Steel locknut

Standard finish:

- Zinc plated

Squeeze type[®] – straight – non-insulated

UL File No. E-19189



FMC fittings

Cat. #	Trade size	Dia. of opening for cable	Dia. of bushed hole	Unit qty.	Wt. lbs. per 100
707 ^{②⑥}	3/8"	5/8"	3/8"	100	7
708 ^{②⑦}	1/2"	15/16"	5/8"	50	14
709	3/4"	1 1/8"	3/4"	20	22
710	1"	1 3/8"	1"	20	31
711	1 1/4"	1 21/32"	1 5/16"	10	46
712	1 1/2"	1 7/8"	1 1/2"	5	79
713	2"	2 1/2"	2"	2	101
714	2 1/2"	2 7/8"	2 3/8"	2	161
715	3"	3 9/16"	3"	1	220
721	3 1/2"	4"	2 13/32"	1	470
722	4"	4 19/32"	3 31/32"	1	610

- ^②UL approved for use with aluminum interlocking grounding metal-clad cable, Type MCIA (Southwire MCAP[™]). MCAP[™] is a registered trademark of Southwire Company.
- ^⑤UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class I, Division 2, NEC 501-4(b).
- ^⑥Suitable for use with armored cable.
- ^⑦Suitable for use with metal-clad cable.

Squeeze type[®] – straight – insulated

UL File No. E-19189



Cat. #	Trade size	Dia. of opening for cable	Dia. of bushed hole	Unit qty.	Wt. lbs. per 100
1707 ^{②⑥}	3/8"	5/8"	3/8"	100	8
1708 ^{②⑦}	1/2"	1 5/16"	5/8"	50	14
1709	3/4"	1 1/8"	3/4"	20	17
1710	1"	1 3/8"	1"	20	26
1711	1 1/4"	1 21/32"	1 5/16"	10	42
1712	1 1/2"	1 7/8"	1 1/2"	5	77
1713	2"	2 1/2"	2"	2	100
1714	2 1/2"	2 7/8"	2 3/8"	2	160
1715	3"	3 9/16"	3"	1	221
1721	3 1/2"	4"	3 13/32"	1	470
1722	4"	4 19/32"	3 31/32"	1	610

- ^②UL approved for use with aluminum interlocking grounding metal-clad cable, Type MCIA (Southwire MCAP[™]). MCAP[™] is a registered trademark of Southwire Company.
- ^⑤UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class I, Division 2, NEC 501-4(b).
- ^⑥Suitable for use with armored cable.
- ^⑦Suitable for use with metal-clad cable.

Flexible metallic conduit fittings

Squeeze type – zinc die cast

SQUEEZE TYPE – ZINC DIE CAST

Applications:

- Used to squeeze and secure AC/MC cable to a box or enclosure

Features:

- Zinc connectors assembled with die cast locknuts and zinc plated screws
- 105°C temperature rating
- Used with armored cable and flexible metal conduit
- Male threads – NPSM

Standard materials:

- Zinc die cast
- Zinc die cast locknut

Standard finish:

- Natural

Squeeze type[®] – straight – non-insulated

UL File No. E-19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
707DC	3/8"	50	6
708DC	1/2"	25	8
709DC	3/4"	25	11
710DC	1"	10	16
711DC	1 1/4"	10	21
712DC	1 1/2"	5	28
713DC	2"	4	36
714DC	2 1/2"	2	85
715DC	3"	1	109
721DC	3 1/2"	1	144
722DC	4"	1	183

[®]UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class I, Division 2, NEC 501-4(b).

Squeeze type[®] – straight – insulated

UL File No. E-19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
1707DC	3/8"	50	6
1708DC	1/2"	25	8
1709DC	3/4"	25	11
1710DC	1"	10	16
1711DC	1 1/4"	10	21
1712DC	1 1/2"	5	28
1713DC	2"	4	36
1714DC	2 1/2"	2	85
1715DC	3"	1	109
1721DC	3 1/2"	1	144
1722DC	4"	1	183

[®]UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class I, Division 2, NEC 501-4(b).

FMC fittings

Flexible metallic conduit fittings

Squeeze type – zinc die cast

SQUEEZE TYPE – ZINC DIE CAST

Applications:

- Used to squeeze and secure AC/MC cable to a box or enclosure

Features:

- Zinc connectors assembled with die cast locknuts and zinc plated screws
- 105°C temperature rating
- Used with armored cable and flexible metal conduit
- Male threads – NPSM

Standard materials:

- Zinc die cast
- Zinc die cast locknut

Standard finish:

- Natural

Squeeze type[®] 90° angle – insulated

UL File No. 19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
1724DC	3/8"	50	8
1736DC	1/2"	25	11
1738DC	3/4"	10	15
1739DC	1"	5	25
1740DC	1 1/4"	10	41
1741DC	1 1/2"	1	117
1742DC	2"	1	119
1744DC	2 1/2"	1	286
1745DC	3"	1	405
1746DC	3 1/2"	1	560
1747DC	4"	1	642

⁵UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class 1, Division 2, NEC 501-4(b).

Squeeze type[®] 90° angle – non-insulated

UL File No. 19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
724DC ¹	3/8"	50	8
736DC	1/2"	25	11
738DC ²	3/4"	10	15
739DC	1"	5	25
740DC	1 1/4"	10	41
741DC	1 1/2"	1	117
742DC	2"	1	119
744DC	2 1/2"	1	286
745DC	3"	1	405
746DC	3 1/2"	1	560
747DC	4"	1	642

²UL approved for use with aluminum interlocking grounding metal-clad cable, Type MClA (Southwire MCAP[®]).

MCAP[®] is a registered trademark of Southwire Company.

⁵UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class 1, Division 2, NEC 501-4(b).

¹UL approved for use with MC-PCS cable.