

TECHNICAL DATA SHEET

Seal Gaskets, series 5260 and 5260-HT Standard and high temperature solutions

T&B Liquidtight Systems[®]



Standard

High Temp

Features & Benefits:

- Designed for use with T&B Liquidtight Systems fittings and connectors
- · Meets UL and CSA requirements
- Trade sizes from 3/8" to 4" (12mm to 100mm)
- · Designed for use with NPT threaded fittings and connectors
- · UL, CSA & IP ingress protection ratings aligned with industrial enclosures
- · Stainless Steel retainer prevents crushing and distortion of gasketing material

Applications:

Ser. 5260 "Standard" Blue:

- · Used extensively in all liquid-tight applications where excessive temperatures are not present
- · Ideal for use with all Liquid-tight Flexible Metallic Conduits
- · Ideal for use with all Ser. 5200 and 5300 Liquid-tight Fittings
- Typically used in all liquid-tight applications for liquids, oils, and dust

Ser. 5260-HT "High Temperature" Black:

- · Coordinated temperature ratings with Wide and Extreme Temperature LFMC and LT Fittings
- · Ideal for use with LTTU and LTTE Wide Temperature Liquid-tight Flexible Metallic Conduits
- Ideal for use with LTXE and LT6XE Extreme Temperature Liquid-tight Flexible Metallic Conduits
- Ideal for use with Ser. 5300-HT & 5300SST6HT High Temperature Liquid-tight Fittings
- Typically used in applications such as foundries, furnaces, ovens, power distribution equipment, pump stations and skids, extremely hot and cold environments

Construction / Material / Finish:

- · Stainless Steel 316 retainer ring
- Molded Seals: Thermoplastic Rubber
- Colors:
 - Blue Standard Ratings
 - Black High Temperature (-HT) Ratings

Liquid-tight Seal Gaskets provide excellent ingress protection between conduit fittings and enclosures. Provides high performance protection against dust, oils, liquids, washdown and extreme temperature environments.

Certifications / Standards:



Environment rating:

Working Temperature:

- UL (Std & HT): -20 to +105°C(-4 to +221°F)
- CSA (Std & HT): -20 to +105°C (-4 to +221°E)
- -60 to +150°C (-76 to +302°F) General (HT):

Chemical Resistance Guide:

See Publication TDS000081

Conforms to:

- · UL 514B, Fittings for Cable and Conduit - File: E23018
- CSA C22.2, No. 18.3, Outlet and Conduit Boxes, Fittings and Accessories - File: LR-4484
- · IEC/EN 60529, Degrees of Protection (IP Code) Seal Gaskets used in ingress testing of T&B Liquid-tight Fittings
- RoHS (Restriction of Hazardous Substance directive)

Standards requirements:

Designed to UL 514B, UL 50E and CSA C22.2 No. 18.3 standard requirements including:

· Oil immersion, exclusion, hardness, tensile strength and elongation tests

Ingress protection:

- · Provides "Ingress Integrity" between liquid-tight fittings and enclosure walls, either NPT threaded entries or knockouts
- Covers all trade sizes from ³/₈" to 4" (12mm to 103mm)

System ingress ratings:

- Products tested and comply with UL 50E and CSA C22.2 No. 94.2 Type Rating requirements
- Indoor: Type 4, 4X, 12, 13
- Outdoor: Type 3, 3R, 4, 4X
- Type 3, 3R, 4, 4X, 12, 13 NEMA 250:

IEC system ingress ratings:

- IP Ingress Protection per IEC/EN 60529 requirements
- IEC Ingress Ratings: IP66, IP67

Figure 1:





Figure 2:



Part No./GID	Dimension Trade Size NPT Fi				Figure	re Dimensions				
	UL Inches	CSA mm	ISO/BS EN mm	Thread	, igure	A Inches (mm)	B Inches (mm)	C Inches (mm)	D Inches (mm)	Weight Ibs (kg)
Standard - Blue										
5299 *	1/4	10	12	1/4"	1	13/16	9/16	-	7/64	0.005
7TAD012420R0040	_					(20.3)	(14.1)		(2.8)	(0.002)
5261 *	3/8	12	16	3/8"	1	31/32	11/16	-	7/64	0.006
7TAD012060R0000						(24.4)	(17.5)		(2.8)	(0.003)
5262	1/2	16	20	1/2"	2	1-5/32	7/8	3/4	11/64	0.008
7TAD012070R0000						(29.5)	(21.8)	(19.1)	(4.5)	(0.004)
5263	3/4	21	25	3/4"	2	1-1/2	1-1/16	15/16	3/16	0.016
7TAD012070R0001						(37.8)	(27.2)	(23.6)	(4.9)	(0.007)
5264	1	27	32	1"	2	1-3/4	1-11/32	1-1/8	³ /16	0.018
7TAD012070R0002						(44.5)	(33.9)	(29.7)	(4.9)	(0.008)
5265	1-1/4	35	40	1-1/4"	2	2-5/32	1-11/16	1-33/64	7/32	0.025
7TAD012070R0003						(54.6)	(42.7)	(38.6)	(5.6)	(0.011)
5266	1-1/2	41	50	1-1/2"	2	2-7/16	$1^{-15/16}$	$1^{-3/4}$	¹⁵ / ₆₄	0.030
7TAD012070R0004						(61.5)	(49.1)	(44.5)	(5.8)	(0.014)
5267	2	53	63	2"	2	$2^{-15/16}$	2-11/32	2-1/2	¹⁵ / ₆₄	0.064
7TAD012070R0005						(74.2)	(59.4)	(56.6)	(5.8)	(0.029)
5268	2-1/2	63	70	2-1/2"	1	3-7/16	2- ²⁹ /32	-	¹⁵ / ₆₄	0.050
7TAD012060R0001						(87.4)	(73.9)		(5.8)	(0.023)
5269	3	78	80	3"	1	4-¹/16 (103.6)	3-17/32 (89.9)	-	¹⁵ ⁄64 (5.8)	0.055 (0.025)
7TAD012060R0002									(5.6)	(0.023)
5270	4	103	100	4"	1	5-%32 (134.4)	4-%16 (115.6)	-	⁵⁄16 (7.9)	0.138 (0.062)
7TAD012060R0003						(134.4)	(115.0)		(1.5)	(0.002)
High Temp - Black										
5261-HT *	3/8	12	16	3/8"	1	^{31/₃₂} (24.4)	^{11/16} (17.5)	-	⁷ ⁄ ₆₄ (2.8)	0.006 (0.003)
5262-HT	1/2	16	20	1⁄2"	2	1-5/32 (29.5)	7⁄₅ (21.8)	³ ⁄4 (19.1)	¹¹ / ₆₄ (4.5)	0.008 (0.004)
5263-HT	3/4	21	25	3/4"	2	1-½ (37.8)	1-1/16 (27.2)	^{15/} 16 (23.6)	³ /16 (4.9)	0.016 (0.007)
5264-HT	1	27	32	1"	2	1-¾ (44.5)	1-11/32 (33.9)	1-1/8 (29.7)	³ /16 (4.9)	0.018 (0.008)
5265-HT	1-1/4	35	40	1-1⁄4"	2	2-5/32 (54.6)	1- ¹¹ /16 (42.7)	1- ³³ ⁄64 (38.6)	7⁄₃₂ (5.6)	0.025 (0.011)
5266-HT	1-1/2	41	50	1-1⁄2"	2	2-1/16 (61.5)	1- ^{15/} 16 (49.1)	1-¾ (44.5)	¹⁵ ⁄ ₆₄ (5.8)	0.030 (0.014)
5267-HT	2	53	63	2"	2	2-15/16 (74.2)	2-11/32 (59.4)	2-½ (56.6)	¹⁵ / ₆₄ (5.8)	0.064 (0.029)
5268-HT	2-1/2	63	70	2-1⁄2"	1	3-7⁄16 (87.4)	2- ^{29/} 32 (73.9)	-	¹⁵ / ₆₄ (5.8)	0.050 (0.023)
5269-HT	3	78	80	3"	1	4-¹/ ₁₆ (103.6)	3- ¹⁷ / ₃₂ (89.9)	-	¹⁵ / ₆₄ (5.8)	0.055 (0.025)
5270-HT	4	103	100	4"	1	5- ⁹ /32 (134.4)	4-%/16 (115.6)	-	⁵ /16 (7.9)	0.138 (0.062)

Note: Product must be installed in accordance with applicable national and local electrical codes. *Not UL Listed

tnb.abb.com tnb.ca.abb.com abb.com We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. Copyright© 2019 ABB. All rights reserved.