

Lug Information

Aluminum Body Lugs for Copper or Aluminum Wire

Selection

For Use With Type(s)	Circuit Breaker Ampere Rating	Cables Per Lug	Lug Wire Range	Catalog Number	List Price \$
QJ2, QJH2 QJ2H, HQJ2H	60–225	1	#6 AWG–300 kcmil (Cu) #4 AWG–300 kcmil (Al)	TA1Q300	
All 2, 3 pole ED2, ED4, ED6, ED6 ETI, HED4, HHED6	15–25	1	#14–#10 AWG (Cu) #12–#10 AWG (Al)	SA1E025	
	30–100	1	#10–#1/0 (Cu or Al)	LN1E100	
	110–125	1	#3-3/0 (Cu) #1-2/0 (Al)	TA1E6125	
CED6 All 1 pole ED, HED	30–60	1	#10–4 (Cu or Al)	LD1E060 (Load Side)	
	70–100	1	#4–#1/0 (Cu or Al)	LD1E100 (Load Side)	
FXD6-A, FD6-A, HFD6, CFD6 HHFD6	70–250	1	#6 AWG–350 kcmil (Cu) #4 AWG–350 kcmil (Al)	TA1FD350A	
SJD6(A), SHJD6(A) SCJD6	65–200	1–2	#4 AWG–310 kcmil (Cu or Al)	TA2J630	
JXD2(A), JXD6(A), JD6(A), SJD6(A), HJD6(A), HHJD6, HHJD6, SHJD6(A), CJD6, SCJD6	200–400	1–2	3/0–500 kcmil (Cu) 4/0–500 kcmil (Al)	TA2J6500	
LXD6(A), LD6(A), SLD6(A), HLD6(A), HHLXD6, HHLD6, SHLD6(A), CLD6, SCLD6	250–600	1–2	3/0–500 kcmil (Cu) 4/0–500 kcmil (Al)	TA2J6500	
LMD6 ^① , LMXD6 ^① , HLMd6 ^① , HLMXD6 ^① , MD6, MXD6, SMD6, HMD6, HMXD6, SHMD6, CMD6, SCMD6	500–600	1–2	250–500 kcmil (Cu or Al)	TA2K500	
	700–800	1–3	1/0–500 kcmil (Cu or Al) 500–750 kcmil (Cu or Al)	TA3K500 TA2N750 ^②	
ND6, NXD6, SND6, HND6, HNXD6, SHND6, CND6, SCND6	800–1200	1–4	250–500 kcmil (Cu or Al)	2TA4P8500 ^③ 3TA4P8500 ^④	
			250–500 kcmil (Cu or Al)	2TA4N8500 ^③ 3TA4N8500 ^④	
PD6, HPD6, CPD6 PXD6, HPXD6, SPD6, SHPD6	1200–1600	1–5	300–600 kcmil (Cu or Al)	TA5P600	
PD6, PXD6, HPD6, HPXD6, SPD6, SHPD6, RD6, RXD6, HRD6, HRXD6, STD	1200–2000	1–6	300–600 kcmil (Cu or Al)	TA6R600	

①Use TA2K500 or TA3K500 only.
②Used for 100% rated MD/ND frame breakers.

③Contains 2 connectors plus 1 NDTS end barrier.
④Contains 3 connectors plus 1 NDTS end barrier.