

# CR-M3SS

## General Information

<b>Extended Product Type:</b>	CR-M3SS
<b>Product ID:</b>	1SVR405651R2000
<b>EAN:</b>	4013614373794
<b>Catalog Description:</b>	CR-M3SS Standard socket
<b>Long Description:</b>	The CR-M3SS socket is from the CR-M (miniature) relay range. The standard socket is suitable for CR-M relays with 3 c/o (SPDT) output contacts. The socket has screw connection terminals. Pluggable function modules, holder and marker are available as accessories.



## Categories

Products » Low Voltage Products and Systems » Control Products »  
Electronic Relays and Controls » Interface Relays and Optocouplers

## Ordering

<b>EAN:</b>	4013614373794
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85389099

## Dimensions

<b>Product Net Width:</b>	27.0 mm
<b>Product Net Height:</b>	42.5 mm
<b>Product Net Depth:</b>	82.0 mm
<b>Product Net Weight:</b>	0.068 kg

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	141.0 mm
<b>Package Level 1 Height:</b>	95.0 mm
<b>Package Level 1 Length:</b>	78.0 mm
<b>Package Level 1 Gross Weight:</b>	0.682 kg

## Technical

<b>Function:</b>	Accessory for interface relays CR-M
<b>Sub-Function:</b>	Socket for miniature relays
<b>Sub-Function 2:</b>	Standard socket for miniature relay 3 c/o
<b>Output:</b>	none
<b>Output Signal:</b>	none
<b>Terminal Type:</b>	Screw Terminals

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

**Certificates and Declarations (Document Number)**

---

<b>cUR Certificate:</b>	cUR_E244328
<b>Declaration of Conformity - CE:</b>	1SAD938500-0159
<b>GOST Certificate:</b>	GOST_POCC_DE.AB76.D02256
<b>RMRS Certificate:</b>	RMRS_12.04008.250
<b>RoHS Information:</b>	1SAA981041-4402
<b>UR Certificate:</b>	UR_E244328

---

**Classifications**

---

<b>Object Classification Code:</b>	K
<b>E-nummer:</b>	4005372
<b>ETIM 4.0:</b>	EC001456 - Relay socket
<b>ETIM 5.0:</b>	EC001456 - Relay socket
<b>UNSPSC:</b>	39120000

---