


## GFCIs

## Isolated-Ground Self-Test GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 &amp; 20A, 125VAC



1597IGTRO

2097IGTRO


## Features

- GFCI receptacle's grounding system is isolated from the building's grounding system.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Pre-stripped stranded wire lead for isolated ground termination.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

## Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trio Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC			 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
TRADEMASTER® ISOLATED GROUND TAMPER-RESISTANT DUPLEX GFCI							
1597IGTRI	15	125	Ivory	5-15R	•	•	•
1597IGTRW	15	125	White	5-15R	•	•	•
1597IGTRLA	15	125	Light Almond	5-15R	•	•	•
1597IGTROCC4	15	125	Orange	5-15R	•	•	•
SPECIFICATION GRADE ISOLATED GROUND TAMPER-RESISTANT DUPLEX GFCI							
2097IGTRI	20	125	Ivory	5-20R	•	•	•
2097IGTRW	20	125	White	5-20R	•	•	•
2097IGTRGRY	20	125	Gray	5-20R	•	•	•
2097IGTRBK	20	125	Black	5-20R	•	•	•
2097IGTRO	20	125	Orange	5-20R	•	•	•
2097IGTRLA	20	125	Light Almond	5-20R	•	•	•
HOSPITAL GRADE ISOLATED GROUND TAMPER-RESISTANT DUPLEX GFCI							
1597IGHGTRO	15	125	Orange	5-15R	•	•	•
2097IGHGTRI	20	125	Ivory	5-20R	•	•	•
2097IGHGTRW	20	125	White	5-20R	•	•	•
2097IGHGTRGRY	20	125	Gray	5-20R	•	•	•
2097IGHGTRRED	20	125	Red	5-20R	•	•	•
2097IGHGTRO	20	125	Orange	5-20R	•	•	•
2097IGHGTRLA	20	125	Light Almond	5-20R	•	•	•



## National Electrical Code® Section 406.12 Tamper-Resistant Receptacles in Dwelling Units.


In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory

Light Almond


White

Green

Antique Brass

Dark Bronze

Nickel



Black

Blue

Brown

Gray


Orange

Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates

#### Metal Finish



Aluminum

Brass (Brushed)

Polished Brass


Stainless Steel

Brushed Bronze

Chrome

### Custom Metal Wall Plates Paint Finish Colors

#### Paint Color



Orange

Green

Gray

Yellow

Glossy Black

Brown

White



Primer

Red

Pink

Flat Black

Ivory

Light Almond

Blue

To order custom metal wall plates, see Pages P-40 – P-42.

**For additional colors consult factory.**