

OS600J03

ABB contact for Canada [Print to Pdf..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	OS600J03
Product ID:	1SCA022825R8610
EAN:	6417019284026
Catalog Description:	OS600J03 Fusible disconnect switch
Long Description:	Including terminal bolt kit as standard. The handle and shaft have to be ordered separately.



Categories

Products » Low Voltage Products and Systems » Switches » Switch Fuses

Ordering

EAN:	6417019284026
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Dimensions

Product Net Width:	343 mm
Product Net Height:	306 mm
Product Net Depth:	233 mm
Product Net Weight:	13 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	328 mm
Package Level 1 Height:	260 mm
Package Level 1 Length:	365 mm
Package Level 1 Gross Weight:	13 kg
Package Level 1 EAN:	6417019284026

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
---------------------	---

Technical UL/CSA

Ampere Rating UL/CSA:	600 A
Horse Power Rating UL/CSA:	acc. to UL 240V 200 Hp acc. to UL 480V 400 Hp acc. to UL 600V 500 Hp

Additional Information

Conventional Free-air Thermal Current (I_{th}):	q=40°C 630 A
Conventional Thermal Current (I_{the}):	Fully Enclosed 570 A

Fuse Size:	600 A
Fuse Type:	J
Handle Type:	Not included
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Normal
Number of Poles:	3
Operating Mechanism:	Mechanism at the end of the switch
Operating Mode:	Front Operated
Pollution Degree:	3
Position of Line Terminals:	Top in - bottom out
Power Loss:	46 W
Product Main Type:	OS600
Product Name:	Fusible disconnect switch
Rated Impulse Withstand Voltage (U_{imp}):	12 kV
Rated Insulation Voltage (U_i):	1000 V
Rated Operational Current AC-23A (I_e):	(500 V) 630 A (690 V) 630 A
Rated Operational Power AC-23A (P_e):	(220 ... 240V) 200 kW (400V) 355 kW (415V) 355 kW (500V) 450 kW (690V) 630 kW
Rated Operational Voltage:	690 V AC
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 20 kiloampere rms
Standards:	UL
Terminal Type:	Lug terminals

Classifications

ETIM 5.0:	EC001040 - Fuse switch disconnecter
Object Classification Code:	Q