

CR-U024DC3L

General Information

Extended Product Type:	CR-U024DC3L
Product ID:	1SVR405622R1100
EAN:	4013614498589
Catalog Description:	CR-U024DC3L Pluggable interface relay
Long Description:	The CR-U024DC3L pluggable interface relay is from the CR-U (universal) relay range. This relay operates with a 24 V DC rated control supply voltage and has 3 c/o (SPDT) output contacts rated at 250 V / 10 A. The relay has an integrated blue test button for manual actuation and locking of the output contacts and an integrated LED. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

EAN:	4013614498589
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900

Dimensions

Product Net Width:	35.0 mm
Product Net Height:	54.4 mm
Product Net Depth:	35.0 mm
Product Net Weight:	0.083 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	182.0 mm
Package Level 1 Height:	76.0 mm
Package Level 1 Length:	77.0 mm
Package Level 1 Gross Weight:	0.870 kg
Package Level 1 EAN:	4013614374289

Technical

Function:	Pluggable universal interface relay CR-U
Sub-Function:	Relay with built in LED
Output:	3 c/o (SPDT) contacts
Output Signal:	250 V / 10 A
Rated Control Supply Voltage (U_s):	24 V DC

Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CCC Certificate: CCC_2012010303554029
CSA Certificate: CSA_1587291
Declaration of Conformity - CE: 1SAD938500-0159
GOST Certificate: GOST_POCC_DE.AB76.D02256
LR Certificate: LR_05_20002_E2
RMRS Certificate: RMRS_12.04008.250
RoHS Information: 1SAA981040-4403
UR Certificate: UR_E244330
VDE Certificate: VDE_40019116

Classifications

Object Classification Code: K
E-nummer: 4005423
ETIM 4.0: EC001437 - Switching relay
ETIM 5.0: EC001437 - Switching relay
UNSPSC: 39121500
