## LIGHTOLIER


by (Signify

# Track Lighting

Lytespan

6190 Monopoint, Basic

Project:		
Location:		
Cat.No:		
Туре:		
Lamps:	Qty:	
Natar.		



### **Ordering Information**

Catalog No.	Finish	Junction Box Mounting	Compatibility
6190WH	Matte White	4" & 3 1/2" Octagonal,	Lytespan Track Luminaires. See individual
6190BK	<sup>I</sup> Matte Black	4" & 3 1/2" Round	spec sheets for compatibility with Monopoints
6190AI	Matte Aluminum		

# 6190 Lytespan

### Monopoint, Basic

### **Features**

- Basic Lytespan Track Strip: Die-cast with high-temperature impact-resistant thermoplastic insulator, supporting electrical contacts. Accepts Lytespan luminaires for individual applications.
- 2. Junction Box Canopy: Steel low-profile canopy, attached with two painted slotted cap screws (provided).
- 3. Crossbar: 0.074 steel, permanently fixed to track. Provides secure mounting of monopoint to electrical junction box.
- 4. Supply Leads: 16ga. White and Black, 18ga. Green; insulated stranded
- 5. Locking Slot: Accepts locking tab of some Lytespan Track luminaires.

#### **Finish**

All Painted finishes are baked enamel.

### **Electrical**

Capacity is 120volts, 60Hz, 660W max. All Lytespan Track luminaires are polarized and continuously grounded throughout. Electrical conductors are concealed in an insulating liner. Intended for wiring to branch circuit building wire with ground. All wiring must be in accordance with National and Local Codes.

Use 90°C minimum supply wire to monopoint.

### Labels

U.L. listed, cULus

