

# **HN4 Series Two Door Floormount Enclosures - NEMA 4**

Continuous Hinge, 3pt Handle



Inner Panel Included







## **Application**

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in outdoor applications for full weather protection.

#### **Standards**

- UL 508 Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- Complies with
  - NEMA Type 3R, 4 12 and 13
  - IEC 60529, IP66

### Construction

- Formed 12 gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Lifting eyes provide for easy enclosure handling.
- Doors are supported with heavy gauge continuous hinges.
- 3-pt padlocking door handle.
- Seamless poured-in place gasket.
- · Provision for light kit mounting.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the inner panel.
- 12" floor stands are welded to the enclosure.
- Body stiffeners are provided in the larger enclosures for extra rigidity.
- Formed lip on door and top of enclosure opening exclude flowing liquids and contaminants.
- A removable 10 gauge inner panel is included.
- Panel supports are provided for easy panel installation.
- Collar studs are provided for mounting inner panels.
- A literature pocket is provided for the inside of the door.

#### Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating.
- Removable white inner panel is finished in white powder coating.

#### Accessories


- Air conditioners...see page 349-367
- Blowers...see page 392
- Breather kits...see page 400-401
- Door stop kit...see page 453
- Drip shield kits...see page 451
- Enclosure stabilizers...see page 456
- Filter fans...see page 371-384
- Floor stand kits...see page 453
- Gland Plates...see page 446
- Heaters...see page 393-396
- Inner Panels...see page 437
- Light kit...see page 452
- Louvered ventilating plates ...see page 402
- Thermostats...see page 397
- Window kits...see page 449


Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise




# **HN4 Series Two Door Floormount Enclosures - NEMA 4** Continuous Hinge, 3pt Handle





**Front View** 

**Section Y-Y** 



**Section X-X** 

|             | ·     | Overall Dimensions |       |    | Inner Panel (Included) |  |
|-------------|-------|--------------------|-------|----|------------------------|--|
| Part No.    | А     | В                  | С     | D  | E                      |  |
| HN4FM604810 | 60.13 | 48.06              | 10.69 | 56 | 44                     |  |
| HN4FM606012 | 60.13 | 60.06              | 12.69 | 56 | 56                     |  |
| HN4FM726012 | 72.13 | 60.06              | 12.69 | 68 | 56                     |  |
| HN4FM727212 | 72.13 | 72.06              | 12.69 | 68 | 68                     |  |
| HN4FM727224 | 72.13 | 72.06              | 24.69 | 68 | 68                     |  |

Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Data Subject to change without notice