

# Wire Lamp Guards and Wire Lamp Guard Grounding Kit

## Wire Lamp Guards

### Applications

- Wire lamp guards with universal collars help prevent breakage and theft.

### Features

- A wide variety of types and sizes is available to fit your diverse needs.
- Heavy-duty, 10 or 12 gauge, zinc-plated construction ensures long life.
- Easy to install.
- Vinyl coated versions available.
- Rust-resistant zinc plating with chromate finish.
- Clamp type guards for vapor-tight fixtures available.
- Spot welded steel wire ensures long life.

### Certifications and Compliances

- Meets OSHA requirements

## Wire Lamp Guard Grounding Kit










### Application

- To ensure that your lamps are grounded, and comply with NEC and OSHA requirements, the grounding kit supplies a metal fastener and 1' / 0.3 m wire to connect wire lamp guards to a grounding circuit.


### Certifications and Compliances

- Meets OSHA requirements
- Meets NEC requirements

### Wire Lamp Guards

	Description	Collar Diameter Inches/Millimeters	Catalog Number	
			for 100 W Bulb	for 200 W Bulb
	GRIPON guards with out reflectors	1.50/38.1	2100-2100-A	2200-2200-A
	Vinyl coated GRIPON guards with out reflectors	1.50/38.1	V-2100BULK	V-2200BULK
	PROTECTOR "O" guards; open bottom heavy-duty	1.50/38.1	1433	1434
	Vinyl coated PROTECTOR "O" guards	1.50/38.1	V-1433	V-1434
	Trap only to close bottom of 1433 and 1434	—	2932	2933
	Closed bottom wall and receptacle lamp guards	3.50/88.9	1438	—
	Cage for utility light ❶	3.50/88.9	1435-6	—
	Guards for PAR and R-38 lamps	1.69/0.51 — 2.63/0.8	1438-1	—
	Guards for vapor-tight fixtures	3.75/1.14 (1435-1)	1435-1	1435-3 ❷

### Wire Lamp Guard Grounding Kit

	Description	Catalog Number
	Grounding Kit	9995

❶ See McGill Incandescent and Fluorescent Utility Lights. Plastic cages available, see McGill String-O-Lights.

❷ 300 Watt type PS25 lamp only.