

Cable Tie Mounting Bases



Ideal for high-density packaging!

• Simply slip Ty-Rap® cable tie under slot in fastened mount, and attach bundle




Std. Pkg. Cat. No.	Bulk Pkg. Cat. No.	Mounting Method	Maximum Tie Width Accom. (in.)	Width		Length		Std.	Bulk
				(in.)	(mm)	(in.)	(mm)	Pkg.	Pkg.
Low-Profile	Two-Way Minia	ture Mounting B	ases						
TC502	TC102	#8 screw	0.19	0.50	12.70	0.75	19.05	100	
_	TC104	#5 screw	0.09	0.32	8.03	0.41	10.31	_	1.000
_	TC804-TB	#2 screw	0.09					_	
_	TC112-TB	#8 screw	0.19	0.38	9.53	0.75	19.05	_	1,000
_	TC812-TB	#10 screw	0.19					-	
-	TC814-TB	#5 screw	0.19					_	

Threaded insert permits screw to come from outside of mounting surface.

Natural nylon colour.

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).



Cat. No.	Mounting Method	Material	Max. Tie Width Accom.	Width		Length		Std.		
				(in.)	(mm)	(in.)	(mm)	Pkg.		
Miniature Base										
TC817-TB	TC2PA	Nylon 6/6	0.19	0.44	11.10	0.44	11.10	1,000		

Natural nylon colour.

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).



Handles ties installed in either direction



Std. Pkg. Cat. No.	Bulk Pkg Cat. No.	Mounting Method	Maximum Tie Width Accom. (in.)	Width		Length		Std.	Bulk	
				(in.)	(mm)	(in.)	(mm)	Pkg.	Pkg.	
Low-Profile Four-Way Mounting Base										
-	TC826-TB	#8 screw	0.19	0.50	12.70	1.00	25.40	_	1.000	
TC5828	TC828-TB	#8 screw		0.39	9.91	0.88	22.23	100	1,000	

The TC826-TB mounting base can be used to tie bundles running parallel or perpendicular to length of base. The TC828-TB mounting plate also handles ties installed in either direction and is somewhat smaller than TC826. Natural nylon colour.

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).

