

Wallplate families

Rugged design and quality materials make Arrow Hart wallplates the best choice

Whether faced with a commercial, institutional or industrial setting, you will find the desired material, configuration, style, size and color you need



Standard size
Wallplates for precision cuts



Mid-size and oversize
Wallplates for applications that require additional wall coverage



Extra depth
Wallplates to provide a flush fit to the wall when an old work outlet box is used



Specification grade thermoplastic

- Available in both nylon and polycarbonate constructions
- Virtually unbreakable plates reduce installation and replacement costs
- Preferred for industrial, institutional, and other high-traffic areas
- Exclusive time-saving screw catch feature holds mounting screws captive and simplifies installation
- High gloss finish is soil-resistant
- Available in standard size and mid-size configurations with screwless and pre-marked special use versions available



Specification grade metal wallplates

- Constructed of non-corrosive 302/304 Stainless steel, brass or chrome
- Available in standard, mid-size, and oversize configurations with pre-marked special use versions available
- 302/304 Stainless steel is non-magnetic and non-corrosive for rugged durability
- Solid brass is coated with transparent lacquer to resist premature oxidation
- Shipped with removable protective film
- Recommended for industrial, institutional and commercial applications

Same style, same durable quality with CuVerro® antimicrobial copper surfaces

The Arrow Hart line of devices featuring CuVerro® antimicrobial copper surfaces, offer specification grade decorator switches and wallplates in multiple gangs and configurations

Features & benefits



Wallplates with CuVerro® antimicrobial touch surface



Antimicrobial Copper **Cu⁺**

- Touch surfaces constructed of EPA registered⁺⁺ CuVerro® antimicrobial copper
- When cleaned regularly, delivers continuous and ongoing antibacterial⁺ action, remaining effective in killing greater than 99.9% of bacteria⁺ within 2 hours
- Unlike coatings, CuVerro® surfaces are wear resistant and the durable antibacterial⁺ properties will remain effective for as long as the product remains in place and is used as directed
- Tarnish resistant with minimal color change over time
- Surfaces should be cleaned to regular protocols
- Durable enough for hospital grade cleaners

⁺Laboratory testing shows that, when cleaned regularly, CuVerro® antimicrobial copper surfaces kill greater than 99.9% of the following bacteria within 2 hours of exposure: MRSA, Staphylococcus aureus, Enterobacter aerogenes, Pseudomonas aeruginosa, and E. coli O157:H7. CuVerro® antimicrobial copper surfaces are a supplement to and not a substitute for standard infection control practices and have been shown to reduce microbial contamination, but do not necessarily prevent cross contamination; users must continue to follow all current infection control practices, including those practices related to cleaning and disinfection of environmental surfaces. CuVerro® is a registered trademark of GBC Metals, LLC and is used with permission, CW-0013-1207.

⁺⁺EPA Registration Number 85353-5 (7600CUR Series) and 85353-3 (7600CU Series)


Compliances, specifications and availability are subject to change without notice.

www.eaton.com
www.eaton.com/arrowhart


Mid-size decorator wallplates

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang





5-Gang




6-Gang

Decorator wallplates

Gang	Material	Color suffix	Catalog no.		
1-Gang	Polycarbonate	A, B, BK, BL, GY, LA, RD, V, W	<input type="checkbox"/> PJ26__		
	Thermoset	A, B, LA, V, W	<input type="checkbox"/> 2051__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93934		
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	<input type="checkbox"/> PJ262__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2052__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93935		
3-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ263__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2063__		
	302/304 Stainless steel	—	<input type="checkbox"/> 93936		
4-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ264__		
	Thermoset	A, LA, V, W	<input type="checkbox"/> 2064__		
5-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ265__		
6-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	<input type="checkbox"/> PJ266__		

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32