


## WATER BASED FIRESTOP SEALANTS

### 3M™ Fire Barrier Sealant FD 150+

3M™ Fire Barrier Sealant FD 150+ is the economical alternative to costly firestopping applications. Used to firestop metal pipes or cables through concrete or gypsum, and in dynamic head-of-wall systems.

- Firestop tested up to 3 hours in accordance with ASTM E 814 (UL 1479)
- Fire Resistive Joint System tested up to 4 hours in accordance with ASTM E 1966 (UL 2079)
- Water based acrylic latex – easy cleanup and routine disposal
- Safe, solvent-free – fully cured, continuous seal with  $\pm 19\%$  dynamic joint movement capability
- Single-part formulation
- Remains pliable allowing for normal pipe movement
- Fast-drying – tack-free in approximately 30-60 minutes
- Paintable (best results obtained after 72 hour cure)
- Excellent adhesion – multi-viscosity grade offers excellent caulking properties
- Available in limestone gray, blue and red



Not for use with CPVC pipe.

| FIRE BARRIER                           | SMOKE SEAL                                      | SOUND BARRIER                                  | ELASTOMERIC   |
|--|---|--|---|
| UP TO <b>4</b> HOUR<br>Fire Protection | <b>L</b> RATED<br>Meets Optional L Requirements | <b>STC 56</b><br>In STC 56-Rated Wall Assembly | <b><math>\pm 19\%</math></b><br>Movement Capability |

## WATER TIGHT SILICONE FIRESTOP SEALANTS

### 3M™ Fire Barrier Water Tight Sealant 3000 WT

3M™ Fire Barrier Water Tight Sealant 3000 WT Intumescent Sealant forms an effective barrier to fire and water in through penetrations. This high-performance sealant helps prevent water and moisture intrusion while protecting buildings and their occupants by preventing the spread of fire, smoke and toxic gas.

- Intumescent silicone for use in systems with a firestop rating up to 4 hours when tested in accordance with ASTM E 814 (UL1479)
- Meets UL Water Leakage Test, W Rating – Class 1 requirements for systems tested in accordance with ANSI/UL 1479
- Helps prevent moisture and water migration through a building
- Minimizes noise transfer—STC-rating of 53 when tested in STC 54-rated wall assembly
- Excellent weathering properties
- Ideal for fast-track construction
- Easy application with standard caulking gun or pneumatic pump
- Excellent bonding
- Gray color with black flecks

| FIRE BARRIER                           | SMOKE SEAL                                      | WATER BARRIER                                 | SOUND BARRIER                                  |
|--|---|---|--|
| UP TO <b>4</b> HOUR<br>Fire Protection | <b>L</b> RATED<br>Meets Optional L Requirements | <b>CLASS 1W</b><br>Rating<br>UL Water Leakage | <b>STC 53</b><br>In STC 54-rated Wall Assembly |

**FBC**  
SYSTEM COMPATIBLE

