

Device Boxes

Conduit Knockouts




CI425
 "Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



BC1102
 Recessed ears.



CI1102-SB



CI3102-SSX
 "Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.



BC1104
 Recessed ears.



CI1104-B



Cat. No.	Volume (Cu. in.)	Features		Knockouts	
		Ears	Bracket	1/2 in. ends	1/2 in. bottom
2 in. Deep — Gangable — 3 in. x 2 in.					
CI425	10.0	flush	rework	2	-
BC1102	10.0	recessed	-	2	-
CI1102-SB	10.0	-	"SB"	2	-
CI3102-SSX	12.0	-	"SSX"	2	-
2-1/2 in. Deep — Gangable — 3 in. x 2 in.					
BC1104	12.5	recessed	-	2	2
CI1104-B	12.5	-	"B"	2	2

Rework Boxes



CI425

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



CI425-L

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



CI525-L

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



BC775-LD

"Swing-Arm" rework brackets. Max. wall thickness: 3/4 in.



BC777-LRB

Pivoting ends for rework installation. Non-gangable. Max. wall thickness: 1-1/8 in.




BC1004-LRB

Flat sides for rework applications.



BC1104-LRB

Flat sides for rework applications.



BC1104-LRW

Rework bracket for closed wall applications. Max. wall thickness: 1 in.



BC2104-LRB

Flat sides for rework applications. 1 gang.



BC2104-LRB-2

Flat sides for rework applications. 2 gang.



BC54151-LD

"Swing-Arm" rework brackets. Max. wall thickness: 3/4 in. Maximum load capacity: 12 lb. (5.5 kg)



Cat. No.	Volume (Cu. in.)	Dimensions	Features	Knockouts		Pryouts		
		H x W x D (in.)	Clamps	ends	bottom	ends	sides	bottom
Device Boxes								
CI425	10.0	3 x 2 x 2	-	2	1	-	-	-
CI425-L	10.0	3 x 2 x 2	loomex/BX	-	-	4	-	-
CI525-L	12.5	3 x 2 x 2-1/2	loomex/BX	-	-	4	-	-
BC775-LD	10.0	3 x 2 x 2-1/4	loomex	-	1	4	-	-
BC777-LRB*	11.0	3 x 2 x 2-1/4	loomex	-	1	4	-	-
BC1004-LRB	15.0	3 x 2 x 3	loomex/BX	-	1	4	-	-
BC1104-LRB	12.5	3 x 2 x 2-1/2	loomex/BX	-	-	4	-	-
BC1104-LRW	12.5	3 x 2 x 2-1/2	loomex/BX	-	-	4	-	-
BC2104-LRB	12.5	3 x 2 x 2-1/2	loomex/BX	-	-	8	-	-
BC2104-LRB-2	25.0	3 x 4 x 2-1/2	loomex/BX	-	-	16	-	-
Octagonal Boxes								
BC54151-LD	15.0	4 x 4 x 1-1/2	loomex/BX	-	1	-	4	4

* Non-Gangable