

400, 800, 2300 & 2300D SERIES™ RACEWAYS

Two-Piece, Single- and Dual-Channel, Low Profile




Two-piece, single- and dual-channel, low profile raceway. Easy-to-install and ideal for power or communication installations.

CODE REFERENCE

cULus Listed Raceway:
File E90378 Guide RJTX.
Complies with flammability requirements of UL-5A.

Fittings:
File E90377 Guide RJYT.
Meets Article 388 of NEC.
UL Listed for up to 600V.
Meets Section 12-1600 of CEC.

400, 800, 2300 & 2300D Series Raceways System Layout



NOTE: Illustration is for showing product applications only.

KEY

- A. 406, 806, 2306 Cover Clip
- B. 411, 811, 2311, 2311DFO Flat Elbow Fitting
- C. 810A2, 2310A, 2310DFO Entrance End Fitting
- D. 415, 815, 2315 Tee
- E. 417, 817, 2317, 2317DFO Internal Elbow
- F. 418, 818, 2318, 2318DFO External Elbow
- G. 2337A, 2338A Round Device Boxes
- H. 2344, 2347, 2348 Sure-Snap Device Boxes

COLOR OPTIONS




400, 800, 2300 Series Raceway Part Numbers with a "-WH" suffix have a white finish. Part Numbers without a suffix have an ivory finish. 400, 800, 2300 Series Raceways are paintable using latex paint.

Custom color options are also available. Consult the factory for more information.

400, 800, 2300 & 2300D SERIES™ RACEWAYS


Ordering Information

2389A Reducing Connector




For transitioning from 2300 Series Raceway to 400 Series Raceway. Also available in white [2389A-WH].

2317DFO Radiused Divided Internal Elbow




A 90° internal corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations. Also available in white [2317DFO-WH].

2310DFO Radiused Divided Entrance End Fitting




Divided fitting to feed 2300 and 2300 Divided Series Raceway. Includes 1/2", 3/4", and 1" trade size KOs on back and top. Also available in white [2310DFO-WH].

2318DFO Radiused Divided External Elbow



A 90° external corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations. Also available in white [2318DFO-WH].


2311DFO Radiused Divided Flat Elbow



A 90° flat corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations. Also available in white [2311DFO-WH].


400/800/2300/2300D Series Raceway Device Box Ordering Information

2336 Blank Cover




Use with any nonmetallic round device box to convert into a junction box. Also available in white [2336-WH].

2338A Fixture Box




For hanging fixtures, smoke/fire alarms and other security devices with 3 1/2" [89mm] or 4 1/16" [103mm] mounting centers. Has 1/2" trade size KO. Not for use with fans. Also available in white [2338A-WH].

2337A Round Box Extension



For hanging fixtures, smoke/fire alarms and other security devices with 3 1/2" [89mm] or 4 1/16" [103mm] mounting centers. 5 1/2" [140mm] diameter with open base. Not for use with fans. Also available in white [2337A-WH].

2344, 2344-2 Extra Deep Device Box



2344 one-gang, 2344-2 two-gang. Two-gang base has rectangular KO to enable extension from existing single-gang flush wallbox and 1/2" and 1" trade size concentric KOs. Accepts industry standard faceplates for switch and communication devices.

CAT. NO.	L	W	GANG
2344	4 3/4" [121mm]	3" [76mm]	1
2344-WH	4 3/4" [121mm]	3" [76mm]	1
2344-2	4 3/4" [121mm]	4 7/8" [124mm]	2
2344-2-WH	4 3/4" [121mm]	4 7/8" [124mm]	2