

## TYPES GB, GBM

### Ground Connector For Copper Cable to Bar


High copper alloy ground connector for joining a range of cable to 1/4" thick bar.\* Type GB separates cable from bar, GBM clamps cable directly on bar surface. One-wrench installation. UL467 Listed. The high copper alloy cast body and DURIUM™ bolts, nuts, and lockwashers make the GB and GBM suitable for direct burial in concrete or ground.



**Type  
GB**



**Type  
GBM**



**Type  
GB**

**Type  
GBM**



E-67

**NOTE:**

\* The GB, GBM, GC, GCM, GL and GZ are all used for joining a range of cable to bar. The catalog numbers in each table accommodate the indicated cable range and up to 1/4" thick bar. Optional bolt lengths are available to accommodate up to 1" thick bar. For bar thicknesses from 1/4" to 1/2", add the suffix "T4" to the catalog number in the table. For bar thicknesses from 1/2" to 1", add the suffix "T8" to the catalog number in the table.

Catalog Number		Cable	H Type GB / GBL	H Type GBM	J	W Type GB/ GBL	W Type GBM	Rec. Torque
Type GB	Type GBM							
<b>GB4C</b>	<b>GBM4C</b>	8 AWG-4 AWG	1-1/2	1-1/2	3/8	1-1/4	1-1/4	240
<b>GB26</b>	<b>GBM26</b>	4 AWG-2/0 AWG	2	1-1/2	3/8	1-1/2	1-1/2	240
<b>GBL30</b> ①	—	4 AWG-300 kcmil	2	—	1/2	1-7/8	—	480
<b>GB29</b>	<b>GBM29</b>	2/0 AWG-250 kcmil	2	2	1/2	2	2	480
<b>GB34</b>	<b>GBM34</b>	300 kcmil-500 kcmil	3	2-1/4	1/2	2-3/8	2-3/8	480

① GBL30 is not UL Listed

## TYPES GC, GCM

### Ground Connector For Two Copper Cables to Bar


High copper alloy ground connector for joining a wide range of two parallel cables to 1/4" thick bar.\* Type GC separates cable from bar, GCM clamps cable to bar surface. One-wrench installation. UL467 Listed. The high copper alloy cast body and DURIUM™ bolts, nuts, and lockwashers make the GC and GCM suitable for direct burial in concrete or ground.



**Type  
GC**



**Type  
GCM**



**Type  
GC**

**Type  
GCM**



**NOTE:**

\* The GB, GBM, GC, GCM, GL and GZ are all used for joining a range of cable to bar. The catalog numbers in each table accommodate the indicated cable range and up to 1/4" thick bar. Optional bolt lengths are available to accommodate up to 1" thick bar. For bar thicknesses from 1/4" to 1/2", add the suffix "T4" to the catalog number in the table. For bar thicknesses from 1/2" to 1", add the suffix "T8" to the catalog number in the table.

Catalog Number		Cable	H Type GC	H Type GCM	J	W Type GC/GCL	W Type GCM	Rec. Torque
Type GC	Type GCM							
<b>GC4C4C</b>	<b>GCM4C</b>	8 AWG-4 AWG	1-1/2	1-1/2	3/8	1-3/8	1	240
<b>GC2626</b>	<b>GCM26</b>	4 AWG-2/0 AWG	2	1-1/2	3/8	1-3/4	1-3/8	240
<b>GCL30</b>	—	5 AWG-300 kcmil	2	—	1/2	1	—	480
<b>GC2929</b>	<b>GCM29</b>	2/0 AWG-250 kcmil	2-1/4	2	1/2	2-1/4	2	480
<b>GC3434</b>	<b>GCM34</b>	300 kcmil-500 kcmil	2-7/8	2-1/4	1/2	2-7/8	2-5/8	480