


T&B Conduit Fittings

Liquatite® Flexible Conduit—Nonmetallic



Type NMC



Recommended industrial applications:

- Machine tools.
- Motor hookups.
- Food processing equipment.
- Extensions from wireways.
- Sensor and microswitch wiring found in control consoles.

Type	Trade Size	Inside Bend Radius	Weight (lb/100ft)	Coil footage Length	I.D. (in.)		O.D. (in.)	
					Min.	Max.	Min.	Max.
NMC038TB	3/8"	2.00"	10	100	.484	.504	.690	.710
NMC050TB	1/2"	3.25"	11	100	.622	.642	.820	.840
NMC075TB	3/4"	4.25"	15	100	.820	.840	1.030	1.050
NMC100TB	1"	6.50"	25	100	1.041	1.066	1.290	1.315
NMC125TB	1-1/4"	8.00"	34	100	1.380	1.410	1.630	1.660
NMC150TB	1-1/2"	9.00"	42	50	1.575	1.600	1.865	1.900
NMC200TB	2"	11.00"	60	50	2.020	2.045	2.340	2.375
NMC050-1000TB	1/2"	3.25"	11	1000	.622	.642	.820	.840
NMC075-500TB	3/4"	4.25"	15	500	.820	.840	1.030	1.050

See technical data next page.

Use with Bullet® Liquidtight Fittings.

*Available in other colours. Consult Customer Service for details.

Type NMC

A general purpose nonmetallic liquidtight conduit offers excellent protection to wiring from abrasion, sunlight, mild acids, alkaline and oils. Often used for air conditioning hook-ups and other outdoor applications.

Construction Type B

NMC is of the helically wound integral Type B construction. It contains a spiral of rigid PVC reinforcement imbedded within the flexible PVC wall.

Type NM Specifications

Type NMC is intended for installation in accordance with CEC Rule 12-1300 to 12-1306 for Liquidtight Flexible Conduit.

-For containment of 600 volt and lower potential circuits.

Working Temperature



-20°C to 80°C/Dry 60°C/Wet 70°C/Oil

Listed. Conforms to Underwriters Laboratories Standard ANSI/UL 1660 type B




Certified. Conforms to CSA 22.2 No. 227.2 type B.

The 3/8 through 1-1/4 in. trade sizes are listed and marked for direct burial and in poured concrete.

Standard Colour

Black



Recommended industrial applications:

- Protection of fiber optic cable.
- Installation of instrumentation and control cable.
- Indoor/outdoor lighting.
- Packaging equipment.
- Marine and shipboard wiring.
- Flexing—component wiring protection on robots, graphic arts equipment, etc.

Type NMT

Type	Trade Size	Inside Bend Radius	Weight (lb/100ft)	Coil footage Length	I.D. (in.)		O.D. (in.)	
					Min.	Max.	Min.	Max.
NMT038TB	3/8"	.7"	6	100	.484	.504	.690	.710
NMT050TB	1/2"	.9"	8	100	.622	.642	.820	.840
NMT075TB	3/4"	1.1"	10	100	.820	.840	1.030	1.050
NMT100TB	1"	1.3"	15	100	1.041	1.066	1.290	1.315
NMT125TB	1-1/4"	1.7"	20	100	1.380	1.410	1.630	1.660
NMT150TB	1-1/2"	1.9"	26	50	1.575	1.600	1.865	1.900
NMT200TB	2"	2.4"	36	50	2.020	2.045	2.340	2.375

*Available in other colours. Consult Customer Service for details.

Type NMT

Type NMT is an Extra Flexible Liquidtight Nonmetallic Tubing. This lightweight tubing cuts easily and installs quickly. It is ideal for wiring protection in tight quarters and for tight bends. The thin flexible PVC skin allows greater movement for many OEM applications. Used for wiring harnesses, laboratory, equipment, fiber optics, etc.

Construction

Co-extruded from both flexible and rigid PVC. The rigid spiral PVC reinforcement is imbedded within the wall of the tubing.

Working Temperature

-20°C to 70°C

UL Recognized.

Standard Colour

Black.